





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-015267	20OCT2015	DW	CW
	BI	ECR-16-017313	07DEC2016	DW	CW
	C	ECR-21-111798	03SEP2021	WQR	CW
	D	ECR-25-246912	27JUN2025	ABS	RB




M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
CONTACT TYPE: CRIMP CONTACT
 - CONTACTS NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 4mm^2$ (AWG26-AWG12)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20300X10XX000)



PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOOD/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考

T2050643101-000		HEEE-064-M		HEEE-064 MALE INSERT HEEE-064 公插	
PART NUMBER 料 号		PART DESCRIPTION 描 述			
CONTROLLED DOCUMENT.		DWN 05MAR2015 David Wang		 TE Connectivity	
		CHK 05MAR2015 Chris Wang			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 05MAR2015 Xiang Xu		NAME HEEE-064-M	
0 PLC ±-		PRODUCT SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ±-		108-137068			
2 PLC ±-		APPLICATION SPEC			
3 PLC ±-		114-137068		A300779C-T2050643101000 -	
4 PLC ±-		WEIGHT			
ANGLES ±-		-			
FINISH		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 1 REV D	