


Captive Screw Type 4 8-32 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX

Captive Screws - 8-32 Thread			
✓	FCXXXX	Length (L)	S.L. +/- .010
	FC0842	5/16	3/32
	FC0843	3/8	5/32
	FC0844	7/16	7/32
	FC0845	1/2	9/32
	FC0846	9/16	11/32
	FC0847	5/8	13/32
	FC0848	11/16	15/32
	FC0849	3/4	17/32
	FC0850	13/16	19/32
	FC0851	7/8	21/32
	FC0852	15/16	23/32
	FC0853	1	25/32
	FC0854	1-1/16	27/32
	FC0855	1-1/8	29/32
	FC0856	1-3/16	31/32
	FC0857	1-1/4	1-1/32

Material		
✓	Material Code (XX)	
	B	Brass
	S	Steel
	SS	Stainless Steel

✓	Compatible Finish (XX)	
	B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.