


5/32 Hex Female Standoff



Hex Code Table		
✓	FCXXXX	Length (L)
	FC203000	1/8
	FC203001	3/16
	FC203002	1/4
	FC203003	5/16
	FC203004	3/8
	FC203005	7/16
	FC203006	1/2
	FC203007	9/16
	FC203008	5/8
	FC203009	11/16
	FC203010	3/4
	FC203011	13/16
	FC203012	7/8
	FC203013	15/16
	FC203014	1
	FC203015	1-1/16
	FC203016	1-1/8
	FC203017	1-3/16
	FC203018	1-1/4
	FC203019	1-5/16
	FC203020	1-3/8
	FC203021	1-7/16
	FC203022	1-1/2
	FC203023	1-9/16
	FC203024	1-5/8
	FC203025	1-11/16
	FC203026	1-3/4
	FC203027	1-13/16
	FC203028	1-7/8
	FC203029	1-15/16
	FC203030	2

Create a part number:

Length	Thread	Material	Finish
FCXXXXXX	XXX	XX	XX
_____ - _____ - _____ - _____			

Thread				
✓	Thread Code (XXX)	Tapped Thru		Longer Parts
		A, B, S	SS	Blind Tap Depth
	080	3/8	1/4	3/16
	256	3/4	5/8	3/16
	440	1	3/4	1/4

Aluminum (A), Brass (B), Steel (S), Stainless Steel (SS)

Material		
✓	Material Code (XX)	
	A	Aluminum
	B	Brass
	S	Steel
	SS	Stainless Steel
	N	Nylon

Tolerances Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Compatible Finish (XX)	
A, B, S, SS	0 - Plain
B, S	5 - Nickel Plate (QQ-N-290)
A	6 - Iridite #14 Gold (MIL-C-5541E)
A	7 - Iridite Clear (MIL-C-5541E)
A	9 - Alodine 1200
B, S	12 - Zinc Clear (ASTM-B-633)
B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
SS	20 - Passivation (MIL-F-14072D)
A	22 - Clear Anodize (MIL-A-8625-TYPE2) (Sulphuric) Hot Water Seal (Clear)
A	24 - Black Anodize (MIL-A-8625)
B, S, SS	26 - Black Oxide
B, S	28 - Zinc Yellow (ASTM-B-633)



Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware

This document is the property of Fascomp Inc. and shall not be reproduced, distributed or used as a basis for manufacturing without written permission from Fascomp Inc.