75 Ω , Differential RF Amplifier 5 - 1800 MHz



MAAM-011297

Rev. V1

Features

- Single Stage, Differential Amplifier
- 5 V, 290 mA Operation
- 17 dB Flat Gain
- Low Noise
- Low Distortion Performance
- Lead-Free SOIC-8EP Plastic Package
- RoHS* Compliant

Applications

CATV Infrastructure

Description

The MAAM-011297 is high gain, high linearity and low noise differential RF amplifier assembled in a SOIC-8EP plastic package. This amplifier provides 17 dB of flat gain with very low noise figure. The differential push-pull topology provides superior 2nd order intermodulation performance.


The MAAM-011297 provides high gain, low noise and low distortion making it ideally suited for 75 Ω infrastructure applications.

Ordering Information^{1,2}

Part Number	Package	
MAAM-011297	Bulk	
MAAM-011297-TR1000	1000 piece reel	
MAAM-011297-TR3000	3000 piece reel	
MAAM-011297-001SMB	sample board	

- 1. Reference Application Note M513 for reel size information.
- 2. All production sample boards include 5 loose parts.

Functional Schematic



Pin Configuration^{3,4}

Pin#	Pin Name	Function	
1	RF _{IN} +	RF Input +	
2, 3	N/C	No Connection	
4	RF _{IN} - RF Input -		
5	RF _{out} -	RF Output - / V _{DD}	
6, 7	N/C	No Connection	
8	RF _{OUT} +	RF Output + / V _{DD}	

- 3. The exposed pad centered on package bottom must be connected to RF and DC ground.
- All pins listed as "No Connection" are not connected electrically inside the package.

1

^{*} Restrictions on Hazardous Substances, compliant to current RoHS EU directive.

75 Ω , Differential RF Amplifier 5 - 1800 MHz



MAAM-011297

Electrical Specifications: T_A = 25°C, V_{DD} = 5 V, Z_0 = 75 Ω Performance specified with input/output balun MABA-011112.

Parameter	Test Conditions	Units	Min.	Тур.	Max.
Gain	5 - 1800 MHz 50 MHz 1218 MHz 1800 MHz	dB	15.9 16.0 15.4	17.0 17.0 17.0 16.8	19.0 19.0 19.5
Tilt	5 - 1800 MHz	dB		0.4	_
Reverse Isolation	5 - 1800 MHz	dB	_	21	_
Input Return Loss	5 - 1800 MHz	dB	_	18	_
Output Return Loss	5 - 1800 MHz	dB	_	18	_
Noise Figure	45 MHz 1800 MHz	dB	_	2.0 3.5	
Output IP2	5 - 1800 MHz, tone spacing 6 MHz P _{OUT} per tone = +13 dBm	dBm	_	60	
Output IP3	5 - 1800 MHz, tone spacing 6 MHz P _{OUT} per tone = +13 dBm	dBm	_	42	_
P1dB	5 - 1800 MHz	dBm	_	24	_
Composite Triple Beat, CTB	79 channels, 0 dB Tilt, 39 dBmV per channel output, QAM to 1000 MHz	dBc	_	-74	
Composite Second Order, CSO	79 channels, 0 dB Tilt, 39 dBmV per channel output, QAM to 1000 MHz	dBc		-75	_
I _{DD}	V _{DD} = 5 V	mA	_	290	350

75 Ω , Differential RF Amplifier 5 - 1800 MHz



MAAM-011297

Rev. V1

Maximum Operating Ratings^{5,6}

Parameter	Absolute Maximum		
Input Power	10 dBm		
V_{DD}	7 V		
I _{DD}	400 mA		
Operating Temperature	-40°C to +85°C		
Junction Temperature ^{7,8}	150°C		

- 5. Exceeding any one or combination of these limits may cause permanent damage to this device.
- MACOM does not recommend sustained operation near these survivability limits.
- 7. Operating at nominal conditions with T $_{\rm J}$ <150°C will ensure MTTF > 1 x 10^6 hours.
- 8. Junction Temperature (T_J) = Case Temperature (T_C) + $\Theta_{JC}^*(V^*I)$ Typical thermal resistance (Θ_{JC}) = 29°C/W.

a) For $T_C = 25^{\circ}C$,

 $T_J = 67^{\circ}C @ 5V, 290 mA$

b) For $T_C = 85^{\circ}C$,

T_J = 127°C @ 5 V, 250 mA

Absolute Maximum Ratings^{5,6}

Parameter	Absolute Maximum		
RF Input Power CW	27 dBm		
V_{DD}	10 V		
Storage Temperature	-55°C to +150°C		

Handling Procedures

Please observe the following precautions to avoid damage:


Static Sensitivity

Integrated Circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these (HBM) Class 1C devices.




Rev. V1

Recommended PCB Layout



Schematic Including Off-Chip Components⁹



9. Pin 3 of MABA-011112 is an unconnected pin.

Parts List

Component	Value	Package	Component	Value	Package
C1 - C6, C9	10 nF	0402	R1, R2	45.3 Ω	0402
C7	0.5 pF	0402	R3, R4	82 Ω	0402
C8	0.7 pF	0402	R5, R6	270 Ω	0402
L1, L2	22 nH	0402	R7, R8	0 Ω	0402
L3	1.8 nH	0402	T1, T2	1:1 Balun ¹⁰	_
L4	1.5 nH	0402			


10. MABA-011112

4




Rev. V1


Typical Performance Curves: V_{DD} = 5 V




Gain to 3 GHz




Input Return Loss




Output Return Loss



Reverse Isolation



Noise Figure







Rev. V1

Typical Performance Curves: $V_{DD} = 5 \text{ V}$


OIP3, P_{OUT} = +13 dBm/tone




CSO Lower, 79 channels + QAM to 1 GHz, 0 dB tilt, 39 dBmV per channel




CTB, 79 channels + QAM to 1 GHz, 0 dB tilt, 39 dBmV per channel




OIP2, $P_{OUT} = +13$ dBm/tone



CSO Upper, 79 channels + QAM to 1 GHz, 0 dB tilt, 39 dBmV per channel




P1dB






Rev. V1

SOIC-8EP†



[†] Reference Application Note S2083 for lead-free solder reflow recommendations. Meets JEDEC moisture sensitivity level 1 requirements. Plating is 100% matte tin over copper.

Recommended PCB Land Pattern



70 ground vias 0.008 inch finished hole diameter All dimensions shown as inches (mm)

75 Ω , Differential RF Amplifier 5 - 1800 MHz



MAAM-011297

Rev. V

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.