


# PXAE183708NB

# Thermally-Enhanced High Power RF LDMOS FET 320 W, 48 V, 1805 – 1880 MHz

### **Description**

The PXAE183708NB is a 320-watt LDMOS FET intended for use in multi-standard cellular power amplifier applications in the 1805 to 1880 MHz frequency band. Features include input and output matching, high gain and thermally-enhanced package with earless flange. Manufactured with an advanced LDMOS process, this device provides excellent thermal performance and superior reliability.





Package Type: PG-HB2SOF-8-1

#### **Features**

- Broadband internal input and output matching
- Asymmetrical Doherty design
  - Main: P<sub>3dB</sub> = 160 W Typ
  - Peak: P<sub>3dB</sub> = 315 W Typ
- Typical Pulsed CW performance, 1880 MHz, 28 V, Doherty configuration, 10  $\mu s$  pulse width, 10% duty cycle, Class AB (main), Class C (peak)
  - Output power at P<sub>1dB</sub> = 320 W
  - Output power at P<sub>3dB</sub> = 430 W
  - Drain efficiency = 60%
  - Gain = 13.5 dB
- Capable of handling 10:1 VSWR @ 28 V, 54 W (1C WCDMA) output power
- Human Body Model Class 2 (per ANSI/ESDA/JEDEC JS-001)
- Integrated ESD protection
- Low thermal resistance
- Pb-free and RoHS compliant

#### **RF Characteristics**

Single-carrier WCDMA Specifications (tested in the Doherty production test circuit)

 $V_{DD} = 28 \text{ V}, I_{DO} = 800 \text{ mA}, P_{OUT} = 54 \text{ W avg}, V_{GS(PEAK)} = 1.5 \text{ V}, f = 1880 \text{ MHz}, 3GPP \text{ signal, channel bandwidth} = 3.84 \text{ MHz}, peak/average} = 10 \text{ MHz}, 20 \text{ MHz$ dB@0.01%CCDF

Characteristic	Symbol	Min.	Тур.	Max.	Unit
Gain	G <sub>ps</sub>	15.3	16	_	dB
Drain Efficiency	ηD	48	50.5	_	%
Adjacent Channel Power Ratio	ACPR	_	-29.5	-25	dBc
Output PAR @ 0.01% CCDF	OPAR	6.8	7.7	_	dB

All published data at T<sub>CASE</sub> = 25°C unless otherwise indicated

ESD: Electrostatic discharge sensitive device—observe handling precautions!





#### **DC Characteristics**

Characteristic	Symbol	Min.	Тур.	Max.	Unit	Conditions
Drain-source Breakdown Voltage	V <sub>BR(DSS)</sub>	65	_	_	V	V <sub>GS</sub> = 0 V, I <sub>DS</sub> = 10 mA
Drain Leakage Current (main)		_	_	1		$V_{DS} = 28 \text{ V}, V_{GS} = 0 \text{ V}$
(peak)	I <sub>DSS</sub>	_	_	10	μΑ	$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$
Gate Leakage Current	I <sub>GSS</sub>	_	_	1	μΑ	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 0 V
On-State Resistance (main)	_	_	0.08	_		
(peak)	R <sub>DS(on)</sub>	_	0.04	_	W	$V_{GS} = 10 \text{ V}, V_{DS} = 0.1 \text{ V}$
Operating Gate Voltage (main)		2.7	2.9	3.3		V <sub>DS</sub> = 28 V, I <sub>DQ</sub> = 800 mA
(peak)	V <sub>GS</sub>	_	1.5	_	V	V <sub>DS</sub> = 28 V, I <sub>DQ</sub> = 0 mA

#### **Maximum Ratings**

Parameter	Symbol	Value	Unit
Drain-source Voltage	V <sub>DSS</sub>	65	
Gate-source Voltage	V <sub>GS</sub>	-6 to +10	V
Operating Voltage	V <sub>DD</sub>	0 to +32	
Junction Temperature	TJ	225	
Storage Temperature Range	T <sub>STG</sub>	-65 to +150	°C

<sup>1.</sup> Operation above the maximum values listed here may cause permanent damage. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the component. Exposure to absolute maximum rating conditions for extended periods may affect device  $reliability. For reliable continuous operation, the device should be operated within the operating voltage range (V_{DD}) specified above. \\$ 

#### **Thermal Characteristics**

Parameter	Symbol Value		Unit Conditions		
Thermal Resistance (main)		0.63		T <sub>CASE</sub> = 70°C, 54 W CW	
Thermal Resistance (peak)	$R_{ heta JC}$	0.20	°C/W	T <sub>CASE</sub> = 70°C, 316 W CW	

#### **Moisture Sensivity Level**

Level	Test Signal	Package Temperature	Unit		
3	IPC/JEDEC J-STD-020	260	°C		


#### **Ordering Information**

Type and Version Order Code		Package Description	Shipping
PXAE183708NB V1 R2	PXAE183708NB-V1-R2	PG-HB2SOF-8-1	Tape & Reel, 250 pcs


<sup>2.</sup> Product's qualification were performed at 225 °C. Operation at T<sub>1</sub> (275 °C) reduces median time to failure.



#### **Typical Performance** (data taken in test fixture)



**Figure 1.** Single-carrier WCDMA Drive-up  $V_{DD} = 28 \text{ V}$ ,  $I_{DQ(MAIN)} = 800 \text{ mA}$ , f = 1880 MHz, 3GPP WCDMA signal, PAR = 10 dB, BW = 3.84 MHz



**Figure 2.** Single-carrier WCDMA Broadband  $V_{DD} = 28 \text{ V}, I_{DQ} = 800 \text{ mA}, P_{OUT} = 47.3 \text{ dBm}, 3GPP WCDMA signal, PAR = 10 dB$ 




Figure 3. Single-carrier WCDMA Broadband  $V_{DD}$  = 28 V,  $I_{DQ}$ = 800 mA,  $P_{OUT}$  = 47.3 dBm, 3GPP WCDMA signal, PAR = 10 dB





Figure 4. CW Performance  $V_{DD} = 28 \text{ V}, I_{DQ} = 800 \text{ mA}$ 



## **Typical Performance** (cont.)



**Figure 5.** Small Signal CW Gain & Input Return Loss  $V_{DD} = 28 \text{ V}, I_{DQ} = 800 \text{ mA}$ 



#### **Load Pull Performance**

Main side load pull performance – pulsed CW signal: 10  $\mu$ sec, 10% duty cycle, 28 V,  $I_{DQ}$  = 850 mA, class AB

			P <sub>1dB</sub>									
	Max Output Power Max Drain Efficiency					Max Output Power						
Freq [MHz]	$Z_S$ $[\Omega]$	Z <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	Ζ <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	
1805	4.4-j10.8	1.2 - j2.5	19.4	52.30	171	57.6	2.4 - j1.3	21.9	50.10	103	68.4	
1842.5	7.4-j13.2	1.2 - j2.7	19.2	52.30	170	56.7	2.1 - j1.5	21.7	50.50	112	67.9	
1880	16.8-j14.6	1.2 - j2.9	19.3	52.20	165	55.9	2.1 - j1.7	21.7	50.30	106	65.8	

			P <sub>3dB</sub>									
			Max C	output Po	wer	Max Drain Efficiency						
Freq [MHz]	$Z_S$ $[\Omega]$	Ζ <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	Z <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	
1805	4.4 - j10.8	1.2 - j2.6	17.3	53.20	209	60.5	2.1 - j1.9	19.3	51.90	155	71.0	
1842.5	7.4 - j13.2	1.2 - j2.9	17.2	53.10	204	58.9	2.0 - j1.7	19.5	51.60	144	70.6	
1880	16.8 - j14.6	1.3 - j3.0	17.4	53.00	200	59.4	2.0 - j1.9	19.4	51.60	143	69.0	

Peak side load pull performance – pulsed CW signal: 10  $\mu$ sec, 10% duty cycle, 28 V,  $V_{GS(PEAK)}$  = 2.4 V, class B


		P <sub>1dB</sub>									
		Max Output Power Max Drain Efficiency									
Freq [MHz]	$Z_S$ $[\Omega]$	Z <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	Z <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]
1805	2.9 - j6.7	2.0 - j4.5	17.4	54.90	306	56.0	2.2 - j1.7	18.9	52.20	164	69.1
1842.5	5.4 - j7.1	2.4 - j4.8	17.6	54.80	305	54.4	2.1 - j2.1	19.2	52.60	181	69.0
1880	8.4 - j4.2	2.4 - j4.9	17.9	54.80	300	55.4	2.1 - j2.2	19.3	52.20	166	68.3

		P <sub>3dB</sub>									
	Max Output Power					Max Drain Efficiency					
Freq [MHz]	Ζ <sub>s</sub> [Ω]	Z <sub>l</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]	Ζ <sub>[</sub> [Ω]	Gain [dB]	P <sub>OUT</sub> [dBm]	P <sub>OUT</sub> [W]	η <b>D</b> [%]
1805	2.9 - j6.7	2.4 - j4.6	15.3	55.70	369	59.1	2.6 - j2.1	16.7	53.70	234	68.8
1842.5	5.4 - j7.1	2.5 - j4.8	15.6	55.60	366	57.7	2.6 - j2.6	16.9	54.20	260	68.3
1880	8.4 - j4.2	2.9 - 5.1	15.7	55.50	357	57.5	2.5 - j2.7	17.1	53.90	245	68.4



# Reference Circuit, 1805 - 1880 MHz

Test Circuit Part Number	LTA/PXAE183708NB-V1
PCB Information	Rogers 4350, 0.508 mm [0.020"] thick, 2 oz. copper, ε <sub>r</sub> = 3.66




Reference circuit assembly diagram (not to scale)



# **Components Information**

Component	Description	Manufacturer	P/N
Input			
C101, C105	Capacitor, 33 pF	ATC	ATC800A330JT250XT
C102, C106	Capacitor, 10 μF, 50 V	Taiyo Yuden	UMK325C7106MM-T
C103, C104	Capacitor, 22 pF	ATC	ATC800A220JT250XT
R101, R102	Resistor, 5.1 ohms	Panasonic Electronic Components	ERJ-8GEYJ5R1V
R103, R104, R105	Resistor, 10 ohms	Panasonic Electronic Components	ERJ-8GEYJ100V
R106	Resistor, 50 ohms	Richardson	C16A50Z4
C801,C802, C803, C804	Capacitor, 1000 pF	Murata Electronics North America	GRM188R71H102KA01J
R801	Resistor, 1K ohms	Panasonic Electronic Components	ERJ-8GEYJ102V
R802	Resistor, 51 ohms	Panasonic Electronic Components	ERJ-8GEYJ510V
R803	Resistor, 1.3K ohms	Panasonic Electronic Components	ERJ-3GEYJ132V
R804	Resistor, 1.2K ohms	Panasonic Electronic Components	ERJ-3GEYJ122V
R805	Resistor, 10 ohms	Panasonic Electronic Components	ERJ-8GEYJ100V
S1, S2	Potentiometer, 2K ohms	Bourns Inc.	3224W-1-202E
S3	Voltage Regulator	Texas Instruments	LM78L05ACM
S4	Transistor	Diodes Incorporated	BCP5616TA
U1	Hybrid coupler	Anaren	X3C20F1-02S
Output			
C201, C202, C203, C204, C208, C209, C214, C215	Capacitor, 10 μF, 100 V	TDK Corporation	C5750X7S2A106M230KB
C205, C206	Capacitor, 2.4 pF	ATC	ATC800A2R4CT250XT
C207, C212, C213	Capacitor, 33 pF	ATC	ATC800A330JT250XT
C210, C211, C216, C217	Capacitor, 220 μF	Panasonic Electronic Components	EEE-FP1V221AP


# Pinout Diagram (top view)



Lead connections for PXAE183708NB



#### Package Outline Specifications - Package PG-HB2SOF-8-1



Top and Side View

**Bottom View** 

Diagram Notes-unless otherwise specified:

- 1. Mold/Dam Bar/Metal protusion of 0.30mm max per side not included.
- 2. Fillets and radii: all radii are 0.3 mm max unless specified otherwise
- 3. Interpret dimensions and tolerances per ISO 8015
- 4. Dimensions are mm
- 5. Exposed metal surface are tin plated, may not be covered by mold compound
- 6. Does not include mold/dam bar/metal protusion.
- 7. All tolerances  $\pm$  0.1mm unless specified otherwise
- 9. All metal surfaces pre-plated, except area of cut
- 9. Lead thickness: 0.25 mm
- 10.Pins: D1, D2 drain; G1, G2 gate; GND ground; V Drain video decoupling, no DC bias



#### Notes & Disclaimer

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.