







(4.00 mm) .1575"

50 Ω HYBRID RF CABLE ASSEMBLY

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?IJ5H

Insulator Material: Black LCP Contact Material:

Copper Alloy
Pin Material: Copper Alloy
Dielectric Material:
Black LCP

Plating: Au over 50 μ" (1.27 μm) Ni Operating Temp Range: -40 °C to +90 °C RoHS Compliant:

Cable (-2): Conductor Size: 26 AWG,

26 AWG, (0.51 mm).020" dia. Conductor Material: Silver and Copper Plated Steel Wire Insulator Diameter: (1.52 mm).060" Insulator Material:

Shield Material: Silver Plated Copper Wire Jacket Material:


Jacket Diameter: (2.54 mm) .100' Bend Radius: 12.8 mm Impedance: 50 Ω Current Rating:

RoHS Compliant:

Mates with:

End 2 Mates:

SMA, MCX, MMCX, SMB5





			END 2 OPTION	END 2 OPTION	END 2 OPTION
NO. OF		İ	All Gold	All Gold	Gold/Nickel Combination
POSITIONS	Α		- 01SP1 = SMA Straight Plug	-02SP1 = MCX Straight Plug	-02SP2
-01	(20.87) .822		- 01RP1 = SMA Right-angle plug	-02RP1 = MCX Right-angle Plug	= MCX Straight Plug -03SP2
-02	(24.87) .979		- 3MA Right-angle plug	= MCA Right-angle Flug	= MMCX Straight Plug
-04	(32.87) 1.294		= SMA Bulkhead Jack	= MMCX Straight Plug	-07SP2
-06	(40.87) 1.609		-01SR1 = SMA Straight Bulkhead Jack,	-03RP1 = SMB Straight I	= SMB Straight Plug
-08	(48.87) 1.924		Sealed, Reversed Polarity	-07SP1 = SMB Straight Plug	
(4.00) .1575 (8.55) .336	A		01SP1 ASSEMBLED	END OPTION SHOWN LENGTH	

This Series is non-standard, non-returnable.