





NOTE:

1. MAX HARDNESS OF COPPER LAYER: 150 KNOOP.
2. ALL DIMENSIONS ARE SYMMETRICAL ABOUT CENTERLINE WITHIN .002 UNLESS OTHERWISE STATED.
3. CONTACT SAMTEC FOR INSERTION TOOLING: CAT-PT-PTX-1XX-X-X

H

	A	B	C
HASL	0.035	.030±.002	0.005 MAX
GOLD	0.035	.032±.002	N/A
SILVER	0.035	.032±.002	N/A
TIN	0.035	.032±.002	N/A

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322