MOSFET

StrongIRFET™ 2 Power-Transistor, 30 V



Features

- Optimized for a wide range of applications
- N-channel, logic level
- 100% avalanche tested
- 175°C rated
- Pb-free lead plating; RoHS compliant
- Halogen-free according to IEC61249-2-21



Product validation

Qualified according to JEDEC Standard

Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DS}	30	V
$R_{DS(on),max}$	4.7	mΩ
I_D	71	A
Q_{oss}	17	nC
Q_G (0V..4.5V)	10	nC



Type/Ordering Code	Package	Marking	Related Links
IPD047N03LF2S	PG-TO252-3	047N03F2	-

Table of Contents

1 Maximum ratings

at T_A=25 °C, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Continuous drain current [1]	I_D	-	-	71 55 19	A	V_{GS}=10 V, T_C=25 °C V_{GS}=10 V, T_C=100 °C V_{GS}=10 V, T_A=25 °C, R_{THJA}=50 °C/W [2]
Pulsed drain current [3]	$I_{D,pulse}$	-	-	284	A	T_A=25 °C
Avalanche energy, single pulse [4]	E_{AS}	-	-	54 107	mJ	I_D=40 A, R_{GS}=25 Ω I_D=20 A, R_{GS}=25 Ω
Gate source voltage	V_{GS}	-20	-	20	V	-
Power dissipation	P_{tot}	-	-	65 3	W	T_C=25 °C T_A=25 °C, R_{THJA}=50 °C/W [2]
Operating and storage temperature	T_j, T_{stg}	-55	-	175	°C	-

[1] Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature as specified. For other case temperatures please refer to Diagram 2. De-rating will be required based on the actual environmental conditions.

[2] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm^2 (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

[3] See Diagram 3 for more detailed information

[4] See Diagram 13 for more detailed information

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	2.3	°C/W	-
Thermal resistance, junction - ambient, 6 cm² cooling area [5)]	R_{thJA}	-	-	50	°C/W	-
Thermal resistance, junction - ambient, minimal footprint	R_{thJA}	-	-	75	°C/W	-

[5)] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm^2 (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

3 Electrical characteristics

at T_j=25 °C, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	30	-	-	V	V_{GS}=0 V, I_D=1 mA
Gate threshold voltage	$V_{GS(th)}$	1.35	1.85	2.35	V	V_{DS}=V_{GS}, I_D=30 µA
Zero gate voltage drain current	I_{DSS}	-	0.1 10	1 100	µA	V_{DS}=30 V, V_{GS}=0 V, T_j=25 °C V_{DS}=30 V, V_{GS}=0 V, T_j=125 °C
Gate-source leakage current	I_{GSS}	-	10	100	nA	V_{GS}=20 V, V_{DS}=0 V
Drain-source on-state resistance	$R_{DS(on)}$	-	4.1 5.1	4.7 7.3	mΩ	V_{GS}=10 V, I_D=40 A V_{GS}=4.5 V, I_D=20 A
Gate resistance	R_G	-	1.9	-	Ω	-
Transconductance [6]	g_{fs}	45	-	-	S	$\|V_{DS}\|\geq 2\|I_D\|R_{DS(on)max}$, I_D=40 A

[6] Defined by design. Not subject to production test.

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	1400	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Output capacitance	C_{oss}	-	290	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Reverse transfer capacitance	C_{rss}	-	80	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Turn-on delay time	$t_{d(on)}$	-	11	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=40 A, $R_{G,ext}$=1.6 Ω
Rise time	t_r	-	10	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=40 A, $R_{G,ext}$=1.6 Ω
Turn-off delay time	$t_{d(off)}$	-	10	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=40 A, $R_{G,ext}$=1.6 Ω
Fall time	t_f	-	6.4	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=40 A, $R_{G,ext}$=1.6 Ω

Table 6 Gate charge characteristics [7]

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	4.9	-	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V
Gate charge at threshold	$Q_{g(th)}$	-	2.6	-	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V
Gate to drain charge	Q_{gd}	-	3.3	-	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V
Switching charge	Q_{sw}	-	5.6	-	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V
Gate charge total [8]	Q_g	-	10	15	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V

Table 6 Gate charge characteristics [7)]

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Gate plateau voltage	$V_{plateau}$	-	3.5	-	V	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 4.5 V
Gate charge total [8)]	Q_g	-	21	32	nC	V_{DD}=15 V, I_D=40 A, V_{GS}=0 to 10 V
Gate charge total, sync. FET	$Q_{g(sync)}$	-	8.9	-	nC	V_{DS}=0.1 V, V_{GS}=0 to 4.5 V
Output charge	Q_{oss}	-	17	-	nC	V_{DS}=15 V, V_{GS}=0 V

7) See "Gate charge waveforms" for parameter definition

8) Defined by design. Not subject to production test.

Table 7 Reverse diode

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_S	-	-	55	A	T_C=25 °C
Diode pulse current	$I_{S,pulse}$	-	-	284	A	T_C=25 °C
Diode forward voltage	V_{SD}	-	0.87	1.0	V	V_{GS}=0 V, I_F=40 A, T_j=25 °C
Reverse recovery time	t_{rr}	-	15	-	ns	V_R=15 V, I_F=40 A, di_F/dt=500 A/µs
Reverse recovery charge	Q_{rr}	-	34	-	nC	V_R=15 V, I_F=40 A, di_F/dt=500 A/µs

4 Electrical characteristics diagrams

Diagram 1: Power dissipation



P_{tot}=f(T_C)

Diagram 2: Drain current



I_D=f(T_C); V_{GS}≥10 V

Diagram 3: Safe operating area



I_D=f(V_{DS}); T_C=25 °C; D=0; parameter: t_p

Diagram 4: Max. transient thermal impedance



Z_{thJC}=f(t_p); parameter: D=t_p/T

Diagram 5: Typ. output characteristics



I_D=f(V_{DS}), T_j=25 °C; parameter: V_{GS}

Diagram 6: Typ. drain-source on resistance



$R_{DS(on)}$=f(I_D), T_j=25 °C; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics



I_D=f(V_{GS}), $|V_{DS}|>2|I_D|R_{DS(on)max}$; parameter: T_j

Diagram 8: Typ. drain-source on resistance



$R_{DS(on)}$=f(V_{GS}), I_D=40 A; parameter: T_j

Diagram 9: Normalized drain-source on resistance



$R_{DS(on)}$=f(T_j), I_D=40 A, V_{GS}=10 V

Diagram 10: Typ. gate threshold voltage



$V_{GS(th)}$=f(T_j), V_{GS}=V_{DS}; parameter: I_D

Diagram 11: Typ. capacitances



C=f(V_{DS}); V_{GS}=0 V; f=1 MHz

Diagram 12: Forward characteristics of reverse diode



I_F=f(V_{SD}); parameter: T_j

Diagram 13: Avalanche characteristics	Diagram 14: Typ. gate charge
	
I_{AS}=f(t_{AV}); R_{GS}=25 Ω; parameter: $T_{j,start}$	V_{GS}=f(Q_{gate}), I_D=40 A pulsed, T_j=25 °C; parameter: V_{DD}

Diagram 15: Drain-source breakdown voltage	Gate charge waveforms
	
$V_{BR(DSS)}$=f(T_j); I_D=1 mA	-

5 Package Outlines



PACKAGE - GROUP NUMBER:	PG-TO252-3-U01	
DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	2.18	2.39
A1	0.00	0.13
b	0.64	0.89
b1	0.76	1.14
c	0.46	0.61
c1	0.40	0.89
D	5.97	6.22
D1	5.21	---
E	6.35	6.73
E1	4.32	---
e	2.29	
e1	4.58	
N	3	
H	9.40	10.41
L	1.40	1.78
L1	0.89	1.27
L2	0.50	1.02

Figure 1 Outline PG-TO252-3, dimensions in mm



Figure 2 Footprint Drawing PG-TO252-3, dimensions in mm

Revision History

IPD047N03LF2S

Revision 2024-09-20, Rev. 1.0

Previous Revision

Revision	Date	Subjects (major changes since last revision)
1.0	2024-09-20	Release of final

Published by
Infineon Technologies AG
81726 München, Germany