MOSFET

StrongIRFET™2 Power-Transistor, 30 V



Features

- Optimized for a wide range of applications
- N-channel, logic level
- 100% avalanche tested
- 175°C rated
- Pb-free lead plating; RoHS compliant
- Halogen-free according to IEC61249-2-21



Product validation

Qualified according to JEDEC Standard

Table 1 Key Performance Parameters

Parameter	Value	Unit
V_{DS}	30	V
$R_{DS(on),max}$	1.05	mΩ
I_D	210	A
Q_{oss}	176	nC
Q_g(0V..4.5V)	108	nC



Type/Ordering Code	Package	Marking	Related Links
IPP011N03LF2S	PG-TO220-3	011N03F2	-

Table of Contents

1 Maximum ratings

unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Continuous drain current [1]	I_D	-	-	210 163 46	A	V_{GS}=10 V, T_C=25 °C V_{GS}=10 V, T_C=100 °C V_{GS}=10 V, T_A=25 °C, R_{THJA}=40 °C/W [2]
Pulsed drain current [3]	$I_{D,pulse}$	-	-	840	A	T_C=25 °C
Avalanche energy, single pulse [4]	E_{AS}	-	-	2514 5028	mJ	I_D=100 A, R_{GS}=25 Ω I_D=50 A, R_{GS}=25 Ω
Gate source voltage	V_{GS}	-20	-	20	V	-
Power dissipation	P_{tot}	-	-	375 3.8	W	T_C=25 °C T_A=25 °C, R_{THJA}=40 °C/W [2]
Operating and storage temperature	T_j, T_{stg}	-55	-	175	°C	-

[1] Rating refers to the product only with datasheet specified absolute maximum values, maintaining case temperature as specified. For other case temperatures please refer to Diagram 2. De-rating will be required based on the actual environmental conditions.

[2] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm^2 (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

[3] See Diagram 3 for more detailed information

[4] See Diagram 13 for more detailed information

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	0.4	°C/W	-
Thermal resistance, junction - ambient, cm² cooling area [5)]	R_{thJA}	-	-	40	°C/W	-
Thermal resistance, junction - ambient, minimal footprint	R_{thJA}	-	-	62	°C/W	-

[5)] Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical in still air.

3 Electrical characteristics

unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	30	-	-	V	V_{GS}=0 V, I_D=10 mA
Gate threshold voltage	$V_{GS(th)}$	1.35	1.85	2.35	V	V_{DS}=V_{GS}, I_D=250 µA
Zero gate voltage drain current	I_{DSS}	-	0.1 10	1 100	µA	V_{DS}=30 V, V_{GS}=0 V, T_j=25 °C V_{DS}=30 V, V_{GS}=0 V, T_j=125 °C
Gate-source leakage current	I_{GSS}	-	10	100	nA	V_{GS}=20 V, V_{DS}=0 V
Drain-source on-state resistance [6]	$R_{DS(on)}$	-	0.91 1.0	1.05 1.5	mΩ	V_{GS}=10 V, I_D=100 A V_{GS}=4.5 V, I_D=50 A
Gate resistance	R_G	-	1.8	-	Ω	-
Transconductance [7]	g_{fs}	200	-	-	S	$\|V_{DS}\|\geq 2\|I_D\|R_{DS(on)max}$, I_D=100 A

[6] $R_{DS(on)}$ is specified at a distance of 1.8 mm distance to the package body; mounting at a larger distance increases the overall package resistance of approximately 0.04 mOhm/mm per leg.

[7] Defined by design. Not subject to production test.

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	15100	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Output capacitance	C_{oss}	-	2910	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Reverse transfer capacitance	C_{rss}	-	720	-	pF	V_{GS}=0 V, V_{DS}=15 V, f=1 MHz
Turn-on delay time	$t_{d(on)}$	-	46	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=100 A, $R_{G,ext}$=1.6 Ω
Rise time	t_r	-	105	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=100 A, $R_{G,ext}$=1.6 Ω
Turn-off delay time	$t_{d(off)}$	-	60	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=100 A, $R_{G,ext}$=1.6 Ω
Fall time	t_f	-	33	-	ns	V_{DD}=15 V, V_{GS}=4.5 V, I_D=100 A, $R_{G,ext}$=1.6 Ω

Table 6 Gate charge characteristics [8]

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	47	-	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V
Gate charge at threshold	$Q_{g(th)}$	-	28	-	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V
Gate to drain charge	Q_{gd}	-	31	-	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V

Table 6 Gate charge characteristics [8]

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Switching charge	Q_{sw}	-	49	-	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V
Gate charge total [9]	Q_g	-	108	162	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V
Gate plateau voltage	$V_{plateau}$	-	3.1	-	V	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 4.5 V
Gate charge total [9]	Q_g	-	224	336	nC	V_{DD}=15 V, I_D=100 A, V_{GS}=0 to 10 V
Gate charge total, sync. FET [9]	$Q_{g(sync)}$	-	95	-	nC	V_{DS}=0.1 V, V_{GS}=0 to 4.5 V
Output charge [9]	Q_{oss}	-	176	-	nC	V_{DS}=15 V, V_{GS}=0 V

[8] See "Gate charge waveforms" for parameter definition

[9] Defined by design. Not subject to production test.

Table 7 Reverse diode

Parameter	Symbol	Values			Unit	Note/ Test Condition
		Min.	Typ.	Max.		
Diode continuous forward current	I_S	-	-	173	A	T_C=25 °C
Diode pulse current	$I_{S,pulse}$	-	-	840	A	T_C=25 °C
Diode forward voltage	V_{SD}	-	0.82	1.0	V	V_{GS}=0 V, I_F=100 A, T_j=25 °C
Reverse recovery time	t_{rr}	-	36	-	ns	V_R=15 V, I_F=100 A, di_F/dt=500 A/µs
Reverse recovery charge	Q_{rr}	-	160	-	nC	V_R=15 V, I_F=100 A, di_F/dt=500 A/µs

4 Electrical characteristics diagrams

Diagram 1: Power dissipation



P_{tot}=f(T_C)

Diagram 2: Drain current



I_D=f(T_C); V_{GS}≥10 V

Diagram 3: Safe operating area



I_D=f(V_{DS}); T_C=25 °C; D=0; parameter: t_p

Diagram 4: Max. transient thermal impedance



Z_{thJC}=f(t_p); parameter: D=t_p/T

Diagram 5: Typ. output characteristics



I_D=f(V_{DS}), T_j=25 °C; parameter: V_{GS}

Diagram 6: Typ. drain-source on resistance



$R_{DS(on)}$=f(I_D), T_j=25 °C; parameter: V_{GS}

Diagram 7: Typ. transfer characteristics



I_D=f(V_{GS}), |V_{DS}|>2|I_D|$R_{DS(on)max}$; parameter: T_j

Diagram 8: Typ. drain-source on resistance



$R_{DS(on)}$=f(V_{GS}), I_D=100 A; parameter: T_j

Diagram 9: Normalized drain-source on resistance	Diagram 10: Typ. gate threshold voltage
	
$R_{DS(on)}$=f(T_j), I_D=100 A, V_{GS}=10 V	$V_{GS(th)}$=f(T_j), V_{GS}=V_{DS}; parameter: I_D

Diagram 11: Typ. capacitances	Diagram 12: Typ. forward characteristics of reverse diode
	
C=f(V_{DS}); V_{GS}=0 V; f=1 MHz	I_F=f(V_{SD})

Diagram 13: Avalanche characteristics	Diagram 14: Typ. gate charge
	
I_{AS}=f(t_{AV}); R_{GS}=25 Ω; parameter: $T_{j,start}$	V_{GS}=f(Q_{gate}), I_D=100 A pulsed, T_j=25 °C; parameter: V_{DD}

Diagram 15: Drain-source breakdown voltage	Gate charge waveforms
	
$V_{BR(DSS)}$=f(T_j); I_D=10 mA	-

5 Package Outlines



PACKAGE - GROUP NUMBER:	PG-TO220-3-U05	
DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	4.25	4.75
A1	1.14	1.40
A2	2.47	2.92
b	0.71	0.97
b1	1.14	1.78
c	0.36	0.61
D	14.32	15.80
D1	8.39	9.20
D2	11.89	12.80
E	9.90	10.67
E1	8.10	8.74
e	2.54	
N	3	
H	6.00	6.70
L	13.00	14.40
L1	3.56	4.06
øP	3.54	3.90
Q	2.54	2.94

NOTES:
DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURRS
GATE BURRS ARE LESS THAN 0.5 mm

Figure 1 Outline PG-TO220-3, dimensions in mm

Revision History

IPP011N03LF2S

Revision 2024-05-23, Rev. 2.0

Previous Revision

Revision	Date	Subjects (major changes since last revision)
2.0	2024-05-23	Release of final

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to: **erratum@infineon.com**

Published by
Infineon Technologies AG
81726 München, Germany

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics (“Beschaffenheitsgarantie”) . With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer’s compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer’s products and any use of the product of Infineon Technologies in customer’s applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer’s technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Information
For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
The Infineon Technologies component described in this Data Sheet may be used in life-support devices or systems and/or automotive, aviation and aerospace applications or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support, automotive, aviation and aerospace device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.