

# IRF9952PbF


## HEXFET® Power MOSFET

- Generation V Technology
- Ultra Low On-Resistance
- Dual N and P Channel MOSFET
- Surface Mount
- Very Low Gate Charge and Switching Losses
- Fully Avalanche Rated
- Lead-Free

### Description

Fifth Generation HEXFETs from International Rectifier utilize advanced processing techniques to achieve extremely low on-resistance per silicon area. This benefit, combined with the fast switching speed and ruggedized device design that HEXFET Power MOSFETs are well known for, provides the designer with an extremely efficient and reliable device for use in a wide variety of applications.


The SO-8 has been modified through a customized leadframe for enhanced thermal characteristics and multiple-die capability making it ideal in a variety of power applications. With these improvements, multiple devices can be used in an application with dramatically reduced board space. The package is designed for vapor phase, infra red, or wave soldering techniques.



|              | N-Ch          | P-Ch          |
|--------------|---------------|---------------|
| $V_{DS}$     | 30V           | -30V          |
| $R_{DS(on)}$ | 0.10 $\Omega$ | 0.25 $\Omega$ |

Recommended upgrade: IRF7309 or IRF7319

Lower profile/smaller equivalent: IRF7509



|                                              |                     | Symbol         | Maximum         |           | Units |
|----------------------------------------------|---------------------|----------------|-----------------|-----------|-------|
|                                              |                     |                | N-Channel       | P-Channel |       |
| Drain-Source Voltage                         |                     | $V_{DS}$       | 30              |           | V     |
| Gate-Source Voltage                          |                     | $V_{GS}$       | $\pm 20$        |           |       |
| Continuous Drain Current⑤                    | $T_A = 25^{\circ}C$ | $I_D$          | 3.5             | -2.3      | A     |
|                                              | $T_A = 70^{\circ}C$ |                | 2.8             | -1.8      |       |
| Pulsed Drain Current                         |                     | $I_{DM}$       | 16              | -10       |       |
| Continuous Source Current (Diode Conduction) |                     | $I_S$          | 1.7             | -1.3      |       |
| Maximum Power Dissipation ⑤                  | $T_A = 25^{\circ}C$ | $P_D$          | 2.0             |           | W     |
|                                              | $T_A = 70^{\circ}C$ |                | 1.3             |           |       |
| Single Pulse Avalanche Energy                |                     | $E_{AS}$       | 44              | 57        | mJ    |
| Avalanche Current                            |                     | $I_{AR}$       | 2.0             | -1.3      | A     |
| Repetitive Avalanche Energy                  |                     | $E_{AR}$       | 0.25            |           | mJ    |
| Peak Diode Recovery dv/dt ②                  |                     | dv/dt          | 5.0             | -5.0      | V/ ns |
| Junction and Storage Temperature Range       |                     | $T_J, T_{STG}$ | -55 to + 150 °C |           |       |

### Thermal Resistance Ratings

| Parameter                     | Symbol          | Limit | Units              |
|-------------------------------|-----------------|-------|--------------------|
| Maximum Junction-to-Ambient ⑤ | $R_{\theta JA}$ | 62.5  | $^\circ\text{C/W}$ |

## Electrical Characteristics @ T<sub>J</sub> = 25°C (unless otherwise specified)


|                                        | Parameter                            |      | Min. | Typ.  | Max.  | Units | Conditions                                                                                                  |
|----------------------------------------|--------------------------------------|------|------|-------|-------|-------|-------------------------------------------------------------------------------------------------------------|
| V <sub>(BR)DSS</sub>                   | Drain-to-Source Breakdown Voltage    | N-Ch | 30   | —     | —     | V     | V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA                                                                |
|                                        |                                      | P-Ch | -30  | —     | —     |       | V <sub>GS</sub> = 0V, I <sub>D</sub> = -250μA                                                               |
| ΔV <sub>(BR)DSS</sub> /ΔT <sub>J</sub> | Breakdown Voltage Temp. Coefficient  | N-Ch | —    | 0.015 | —     | V/°C  | Reference to 25°C, I <sub>D</sub> = 1mA                                                                     |
|                                        |                                      | P-Ch | —    | 0.015 | —     |       | Reference to 25°C, I <sub>D</sub> = -1mA                                                                    |
| R <sub>DS(ON)</sub>                    | Static Drain-to-Source On-Resistance | N-Ch | —    | 0.08  | 0.10  | Ω     | V <sub>GS</sub> = 10V, I <sub>D</sub> = 2.2A ④                                                              |
|                                        |                                      |      | —    | 0.12  | 0.15  |       | V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 1.0A ④                                                             |
|                                        |                                      | P-Ch | —    | 0.165 | 0.250 |       | V <sub>GS</sub> = -10V, I <sub>D</sub> = -1.0A ④                                                            |
|                                        |                                      |      | —    | 0.290 | 0.400 |       | V <sub>GS</sub> = -4.5V, I <sub>D</sub> = -0.50A ④                                                          |
| V <sub>GS(th)</sub>                    | Gate Threshold Voltage               | N-Ch | 1.0  | —     | —     | V     | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA                                                  |
|                                        |                                      | P-Ch | -1.0 | —     | —     |       | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = -250μA                                                 |
| g <sub>fs</sub>                        | Forward Transconductance             | N-Ch | —    | 12    | —     | S     | V <sub>DS</sub> = 15V, I <sub>D</sub> = 3.5A ④                                                              |
|                                        |                                      | P-Ch | —    | 2.4   | —     |       | V <sub>DS</sub> = -15V, I <sub>D</sub> = -2.3A ④                                                            |
| I <sub>DSS</sub>                       | Drain-to-Source Leakage Current      | N-Ch | —    | —     | 2.0   | μA    | V <sub>DS</sub> = 24V, V <sub>GS</sub> = 0V                                                                 |
|                                        |                                      | P-Ch | —    | —     | -2.0  |       | V <sub>DS</sub> = -24V, V <sub>GS</sub> = 0V                                                                |
|                                        |                                      | N-Ch | —    | —     | 25    |       | V <sub>DS</sub> = 24V, V <sub>GS</sub> = 0V, T <sub>J</sub> = 125°C                                         |
|                                        |                                      | P-Ch | —    | —     | -25   |       | V <sub>DS</sub> = -24V, V <sub>GS</sub> = 0V, T <sub>J</sub> = 125°C                                        |
| I <sub>GSS</sub>                       | Gate-to-Source Forward Leakage       | N-P  | —    | —     | ±100  | nA    | V <sub>GS</sub> = ±20V                                                                                      |
| Q <sub>g</sub>                         | Total Gate Charge                    | N-Ch | —    | 6.9   | 14    | nC    | N-Channel<br>I <sub>D</sub> = 1.8A, V <sub>DS</sub> = 10V, V <sub>GS</sub> = 10V ④                          |
|                                        |                                      | P-Ch | —    | 6.1   | 12    |       |                                                                                                             |
| Q <sub>gs</sub>                        | Gate-to-Source Charge                | N-Ch | —    | 1.0   | 2.0   |       |                                                                                                             |
|                                        |                                      | P-Ch | —    | 1.7   | 3.4   |       |                                                                                                             |
| Q <sub>gd</sub>                        | Gate-to-Drain ("Miller") Charge      | N-Ch | —    | 1.8   | 3.5   | nC    | P-Channel<br>I <sub>D</sub> = -2.3A, V <sub>DS</sub> = -10V, V <sub>GS</sub> = -10V                         |
|                                        |                                      | P-Ch | —    | 1.1   | 2.2   |       |                                                                                                             |
| t <sub>d(on)</sub>                     | Turn-On Delay Time                   | N-Ch | —    | 6.2   | 12    | ns    | N-Channel<br>V <sub>DD</sub> = 10V, I <sub>D</sub> = 1.0A, R <sub>G</sub> = 6.0Ω,<br>R <sub>D</sub> = 10Ω ④ |
|                                        |                                      | P-Ch | —    | 9.7   | 19    |       |                                                                                                             |
| t <sub>r</sub>                         | Rise Time                            | N-Ch | —    | 8.8   | 18    |       |                                                                                                             |
|                                        |                                      | P-Ch | —    | 14    | 28    |       |                                                                                                             |
| t <sub>d(off)</sub>                    | Turn-Off Delay Time                  | N-Ch | —    | 13    | 26    | ns    | P-Channel<br>V <sub>DD</sub> = -10V, I <sub>D</sub> = -1.0A, R <sub>G</sub> = 6.0Ω,<br>R <sub>D</sub> = 10Ω |
|                                        |                                      | P-Ch | —    | 20    | 40    |       |                                                                                                             |
| t <sub>f</sub>                         | Fall Time                            | N-Ch | —    | 3.0   | 6.0   | pF    | N-Channel<br>V <sub>GS</sub> = 0V, V <sub>DS</sub> = 15V, f = 1.0MHz                                        |
|                                        |                                      | P-Ch | —    | 6.9   | 14    |       |                                                                                                             |
| C <sub>iss</sub>                       | Input Capacitance                    | N-Ch | —    | 190   | —     |       |                                                                                                             |
|                                        |                                      | P-Ch | —    | 190   | —     |       |                                                                                                             |
| C <sub>oss</sub>                       | Output Capacitance                   | N-Ch | —    | 120   | —     | pF    | P-Channel<br>V <sub>GS</sub> = 0V, V <sub>DS</sub> = -15V, f = 1.0MHz                                       |
|                                        |                                      | P-Ch | —    | 110   | —     |       |                                                                                                             |
| C <sub>rss</sub>                       | Reverse Transfer Capacitance         | N-Ch | —    | 61    | —     | pF    |                                                                                                             |
|                                        |                                      | P-Ch | —    | 54    | —     |       |                                                                                                             |

## Source-Drain Ratings and Characteristics


|                 | Parameter                              |      | Min. | Typ.  | Max. | Units | Conditions                                                                     |
|-----------------|----------------------------------------|------|------|-------|------|-------|--------------------------------------------------------------------------------|
| I <sub>S</sub>  | Continuous Source Current (Body Diode) | N-Ch | —    | —     | 1.7  | A     |                                                                                |
|                 |                                        | P-Ch | —    | —     | -1.3 |       |                                                                                |
| I <sub>SM</sub> | Pulsed Source Current (Body Diode) ①   | N-Ch | —    | —     | 16   |       |                                                                                |
|                 |                                        | P-Ch | —    | —     | 16   |       |                                                                                |
| V <sub>SD</sub> | Diode Forward Voltage                  | N-Ch | —    | 0.82  | 1.2  | V     | T <sub>J</sub> = 25°C, I <sub>S</sub> = 1.25A, V <sub>GS</sub> = 0V ③          |
|                 |                                        | P-Ch | —    | -0.82 | -1.2 |       |                                                                                |
| t <sub>rr</sub> | Reverse Recovery Time                  | N-Ch | —    | 27    | 53   | ns    | N-Channel<br>T <sub>J</sub> = 25°C, I <sub>F</sub> = 1.25A, di/dt = 100A/μs    |
|                 |                                        | P-Ch | —    | 27    | 54   |       |                                                                                |
| Q <sub>rr</sub> | Reverse Recovery Charge                | N-Ch | —    | 28    | 57   | nC    | P-Channel<br>T <sub>J</sub> = 25°C, I <sub>F</sub> = -1.25A, di/dt = 100A/μs ④ |
|                 |                                        | P-Ch | —    | 31    | 62   |       |                                                                                |

### Notes:


- ① Repetitive rating; pulse width limited by max. junction temperature. ( See fig. 23 )
- ② N-Channel I<sub>SD</sub> ≤ 2.0A, di/dt ≤ 100A/μs, V<sub>DD</sub> ≤ V<sub>(BR)DSS</sub>, T<sub>J</sub> ≤ 150°C  
P-Channel I<sub>SD</sub> ≤ -1.3A, di/dt ≤ 84A/μs, V<sub>DD</sub> ≤ V<sub>(BR)DSS</sub>, T<sub>J</sub> ≤ 150°C
- ③ N-Channel Starting T<sub>J</sub> = 25°C, L = 22mH R<sub>G</sub> = 25Ω, I<sub>AS</sub> = 2.0A. (See Figure 12)  
P-Channel Starting T<sub>J</sub> = 25°C, L = 67mH R<sub>G</sub> = 25Ω, I<sub>AS</sub> = -1.3A.
- ④ Pulse width ≤ 300μs; duty cycle ≤ 2%.
- ⑤ Surface mounted on FR-4 board, t ≤ 10sec.




**Fig 1.** Typical Output Characteristics







**Fig 2.** Typical Output Characteristics



**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Typical Source-Drain Diode Forward Voltage




**Fig 7.** Typical On-Resistance Vs. Gate Voltage


**Fig 8.** Maximum Avalanche Energy Vs. Drain Current




**Fig 9.** Typical Capacitance Vs. Drain-to-Source Voltage




**Fig 10.** Typical Gate Charge Vs. Gate-to-Source Voltage




**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Ambient




**Fig 12.** Typical Output Characteristics




**Fig 13.** Typical Output Characteristics




**Fig 14.** Typical Transfer Characteristics




**Fig 15.** Typical Source-Drain Diode Forward Voltage




**Fig 16.** Normalized On-Resistance Vs. Temperature



**Fig 17.** Typical On-Resistance Vs. Drain Current



**Fig 18.** Typical On-Resistance Vs. Gate Voltage




**Fig 19.** Maximum Avalanche Energy Vs. Drain Current


# IRF9952PbF

P-Channel


International  
IR Rectifier



**Fig 20.** Typical Capacitance Vs. Drain-to-Source Voltage



**Fig 21.** Typical Gate Charge Vs. Gate-to-Source Voltage




**Fig 22.** Maximum Effective Transient Thermal Impedance, Junction-to-Ambient





## SO-8 Package Outline

Dimensions are shown in millimeters (inches)



| DIM | INCHES     |       | MILLIMETERS |      |
|-----|------------|-------|-------------|------|
|     | MIN        | MAX   | MIN         | MAX  |
| A   | .0532      | .0688 | 1.35        | 1.75 |
| A1  | .0040      | .0098 | 0.10        | 0.25 |
| b   | .013       | .020  | 0.33        | 0.51 |
| c   | .0075      | .0098 | 0.19        | 0.25 |
| D   | .189       | .1968 | 4.80        | 5.00 |
| E   | .1497      | .1574 | 3.80        | 4.00 |
| e   | .050 BASIC |       | 1.27 BASIC  |      |
| e1  | .025 BASIC |       | 0.635 BASIC |      |
| H   | .2284      | .2440 | 5.80        | 6.20 |
| K   | .0099      | .0196 | 0.25        | 0.50 |
| L   | .016       | .050  | 0.40        | 1.27 |
| y   | 0°         | 8°    | 0°          | 8°   |



### NOTES:


1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: MILLIMETER
3. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
4. OUTLINE CONFORMS TO JEDEC OUTLINE MS-012AA.

⑤ DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.15 [0.006].

⑥ DIMENSION DOES NOT INCLUDE MOLD PROTRUSIONS. MOLD PROTRUSIONS NOT TO EXCEED 0.25 [0.010].


⑦ DIMENSION IS THE LENGTH OF LEAD FOR SOLDERING TO A SUBSTRATE.

### FOOTPRINT



## SO-8 Part Marking

EXAMPLE: THIS IS AN IRF7101 (MOSFET)




# IRF9952PbF


International  
**IR** Rectifier

## SO-8 Tape and Reel

Dimensions are shown in millimeters (inches)



- NOTES:
1. CONTROLLING DIMENSION : MILLIMETER.
  2. ALL DIMENSIONS ARE SHOWN IN MILLIMETERS(INCHES).
  3. OUTLINE CONFORMS TO EIA-481 & EIA-541.



- NOTES :
1. CONTROLLING DIMENSION : MILLIMETER.
  2. OUTLINE CONFORMS TO EIA-481 & EIA-541.

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Consumer market.  
Qualifications Standards can be found on IR's Web site.

International  
**IR** Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105

TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.09/04

[www.irf.com](http://www.irf.com)

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.