AUTOMOTIVE GRADE

AUIRF7769L2TR

Automotive DirectFET® Power MOSFET ②

- Advanced Process Technology
- Optimized for Automotive Motor Drive, DC-DC and other Heavy Load Applications
- Exceptionally Small Footprint and Low Profile
- High Power Density
- Low Parasitic Parameters
- Dual Sided Cooling
- 175°C Operating Temperature
- Repetitive Avalanche Capability for Robustness and Reliability
- Lead free, RoHS and Halogen free
- Automotive Qualified *

$V_{(BR)DSS}$		**100V**
$R_{DS(on)}$	typ.	**2.8mΩ**
	max.	**3.5mΩ**
I_D (Silicon Limited)		**124A**
Q_g (typical)		**200nC**



L8

DirectFET® ISOMETRIC

Applicable DirectFET® Outline and Substrate Outline ①

SB	SC			M2	M4		L4	L6	L8	

Description

The AUIRF7769L2TR combines the latest Automotive HEXFET® Power MOSFET Silicon technology with the advanced DirectFET® packaging to achieve the lowest on-state resistance in a package that has the footprint of a DPak (TO-252AA) and only 0.7 mm profile. The DirectFET® package is compatible with existing layout geometries used in power applications, PCB assembly equipment and vapor phase, infra-red or convection soldering techniques, when application note AN-1035 is followed regarding the manufacturing methods and processes. The DirectFET® package allows dual sided cooling to maximize thermal transfer in automotive power systems.

This HEXFET® Power MOSFET is designed for applications where efficiency and power density are essential. The advanced DirectFET® packaging platform coupled with the latest silicon technology allows the AUIRF7769L2TR to offer substantial system level savings and performance improvement specifically in motor drive, high frequency DC-DC and other heavy load applications on ICE, HEV and EV platforms. This MOSFET utilizes the latest processing techniques to achieve low on-resistance and low Qg per silicon area. Additional features of this MOSFET are 175°C operating junction temperature and high repetitive peak current capability. These features combine to make this MOSFET a highly efficient, robust and reliable device for high current automotive applications.

Base Part Number	Package Type	Standard Pack		Orderable Part Number
		Form	Quantity	
AUIRF7769L2	DirectFET Large Can	Tape and Reel	4000	AUIRF7769L2TR

Absolute Maximum Ratings

Stresses beyond those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only; and functional operation of the device at these or any other condition beyond those indicated in the specifications is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions. Ambient temperature (TA) is 25°C, unless otherwise specified.

	Parameter	Max.	Units
V_{DS}	Drain-to-Source Voltage	100	V
V_{GS}	Gate-to-Source Voltage	±20	
I_D @ T_C = 25°C	Continuous Drain Current, V_{GS} @ 10V (Silicon Limited) ④	124	A
I_D @ T_C = 100°C	Continuous Drain Current, V_{GS} @ 10V (Silicon Limited) ④	88	
I_D @ T_A = 25°C	Continuous Drain Current, V_{GS} @ 10V (Silicon Limited) ③	20	
I_D @ T_C = 25°C	Continuous Drain Current, V_{GS} @ 10V (Package Limited)	375	
I_{DM}	Pulsed Drain Current ⑤	500	
P_D @T_C = 25°C	Power Dissipation ④	125	W
P_D @T_A = 25°C	Power Dissipation ③	3.3	
E_{AS}	Single Pulse Avalanche Energy (Thermally Limited) ⑥	260	mJ
I_{AR}	Avalanche Current ⑤	See Fig. 16, 17, 18a, 18b	A
E_{AR}	Repetitive Avalanche Energy ⑤		mJ
T_P	Peak Soldering Temperature	270	°C
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to + 175	

HEXFET® is a registered trademark of Infineon.
*Qualification standards can be found at www.infineon.com

Thermal Resistance

Symbol	Parameter	Typ.	Max.	Units
$R_{\theta JA}$	Junction-to-Ambient ③	——	45	°C/W
$R_{\theta JA}$	Junction-to-Ambient ⑧	12.5	——	
$R_{\theta JA}$	Junction-to-Ambient ⑨	20	——	
$R_{\theta J\text{-}Can}$	Junction-to-Can ④⑩	——	1.2	
$R_{\theta J\text{-}PCB}$	Junction-to-PCB Mounted	——	0.5	
	Linear Derating Factor ④	0.83		W/°C

Static Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	100	——	——	V	V_{GS} = 0V, I_D = 250μA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	——	0.02	——	V/°C	Reference to 25°C, I_D = 2.0mA
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	——	2.8	3.5	mΩ	V_{GS} = 10V, I_D = 74A ⑦
$V_{GS(th)}$	Gate Threshold Voltage	2.0	2.7	4.0	V	V_{DS} = V_{GS}, I_D = 250μA
$\Delta V_{GS(th)}/\Delta T_J$	Gate Threshold Voltage Coefficient	——	-10	——	mV/°C	
gfs	Forward Transconductance	410	——	——	S	V_{DS} = 25V, I_D = 74A
I_{DSS}	Drain-to-Source Leakage Current	——	——	20	μA	V_{DS} = 100V, V_{GS} = 0V
		——	——	250		V_{DS} = 80V, V_{GS} = 0V, T_J = 125°C
I_{GSS}	Gate-to-Source Forward Leakage	——	——	100	nA	V_{GS} = 20V
	Gate-to-Source Reverse Leakage	——	——	-100		V_{GS} = -20V

Dynamic Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
Q_g	Total Gate Charge	——	200	300	nC	V_{DS} = 50V
Q_{gs1}	Gate-to-Source Charge	——	30	——		V_{GS} = 10V
Q_{gs2}	Gate-to-Source Charge	——	9.0	——		I_D = 74A
Q_{gd}	Gate-to-Drain ("Miller") Charge	——	110	165		See Fig.11
Q_{godr}	Gate Charge Overdrive	——	51	——		
Q_{sw}	Switch Charge (Q_{gs2} + Q_{gd})	——	119	——		
Q_{oss}	Output Charge	——	53	——	nC	V_{DS} = 16V, V_{GS} = 0V
R_G	Internal Gate Resistance	——	1.5	——	Ω	
$t_{d(on)}$	Turn-On Delay Time	——	44	——	ns	V_{DD} = 50V, V_{GS} = 10V ⑦
t_r	Rise Time	——	32	——		I_D = 74A
$t_{d(off)}$	Turn-Off Delay Time	——	92	——		R_G = 1.8Ω
t_f	Fall Time	——	41	——		
C_{iss}	Input Capacitance	——	11560	——	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	——	1240	——		V_{DS} = 25V
C_{rss}	Reverse Transfer Capacitance	——	590	——		f = 1.0 MHz
C_{oss}	Output Capacitance	——	6665	——		V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0 MHz
C_{oss}	Output Capacitance	——	690	——		V_{GS} = 0V, V_{DS} = 80V, f = 1.0 MHz

Notes ① through ⑩ are on page 3

Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	—	—	124	A	MOSFET symbol showing the integral reverse p-n junction diode. 
I_{SM}	Pulsed Source Current (Body Diode) ⑤	—	—	500		
V_{SD}	Diode Forward Voltage	—	—	1.3	V	T_J = 25°C, I_S = 74A, V_{GS} = 0V ⑦
t_{rr}	Reverse Recovery Time	—	75	112	ns	T_J = 25°C, I_F = 74A, V_{DD} = 50V
Q_{rr}	Reverse Recovery Charge	—	220	330	nC	dv/dt = 100A/μs ⑦



③ Surface mounted on 1 in. square Cu board (still air).



⑨ Mounted to a PCB with small clip heatsink (still air)



⑨ Mounted on minimum footprint full size board with metalized back and with small clip heatsink (still air).

① Click on this section to link to the appropriate technical paper.
② Click on this section to link to the DirectFET® Website.
③ Surface mounted on 1 in. square Cu board, steady state.
④ T_C measured with thermocouple mounted to top (Drain) of part.
⑤ Repetitive rating; pulse width limited by max. junction temperature.
⑥ Starting T_J = 25°C, L = 0.09mH, R_G = 25Ω, I_{AS} = 74A.
⑦ Pulse width ≤ 400μs; duty cycle ≤ 2%.
⑧ Used double sided cooling, mounting pad with large heatsink.
⑨ Mounted on minimum footprint full size board with metalized back and with small clip heat sink.
⑩ R_θ is measured at T_J of approximately 90°C.



Fig. 1 Typical Output Characteristics



Fig. 2 Typical Output Characteristics



Fig. 3 Typical On-Resistance vs. Gate Voltage



Fig. 4 Typical On-Resistance vs. Drain Current



Fig 5. Typical Transfer Characteristics



Fig 6. Normalized On-Resistance vs. Temperature



Fig. 7 Typical Threshold Voltage vs. Junction Temperature



Fig 8. Typical Source-Drain Diode Forward Voltage



Fig 9. Typical Forward Trans conductance vs. Drain Current



Fig 10. Typical Capacitance vs. Drain-to-Source Voltage



Fig 11. Typical Gate Charge vs. Gate-to-Source Voltage



Fig 12. Maximum Drain Current vs. Case Temperature



Fig 13. Maximum Safe Operating Area



Fig 14. Maximum Avalanche Energy vs. Temperature



Ri (°C/W)	τi (sec)
0.1080	0.000171
0.6140	0.053914
0.4520	0.006099
1.47e-05	0.036168

Fig 15. Maximum Effective Transient Thermal Impedance, Junction-to-Case



Fig 16. Typical Avalanche Current vs. Pulse Width



Fig 17. Maximum Avalanche Energy vs. Temperature

Notes on Repetitive Avalanche Curves , Figures 16, 17:
(For further info, see AN-1005 at www.infineon.com)

1. Avalanche failures assumption:
   Purely a thermal phenomenon and failure occurs at a temperature far in excess of T_{jmax}. This is validated for every part type.
2. Safe operation in Avalanche is allowed as long as T_{jmax} is not exceeded.
3. Equation below based on circuit and waveforms shown in Figures 18a, 18b.
4. $P_{D\ (ave)}$ = Average power dissipation per single avalanche pulse.
5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6. I_{av} = Allowable avalanche current.
7. ΔT = Allowable rise in junction temperature, not to exceed T_{jmax} (assumed as 25°C in Figure 16, 17).
   t_{av} = Average time in avalanche.
   D = Duty cycle in avalanche = $t_{av} \cdot f$
   $Z_{thJC}(D, t_{av})$ = Transient thermal resistance, see Figures 15)

$$P_{D\ (ave)} = 1/2\ (\ 1.3 \cdot BV \cdot I_{av}) = \Delta T/\ Z_{thJC}$$
$$I_{av} = 2\Delta T/\ [1.3 \cdot BV \cdot Z_{th}]$$
$$E_{AS\ (AR)} = P_{D\ (ave)} \cdot t_{av}$$



Fig 18a. Unclamped Inductive Test Circuit



Fig 18b. Unclamped Inductive Waveforms



Fig 19a. Gate Charge Test Circuit



Fig 19b. Gate Charge Waveform



Fig 20a. Switching Time Test Circuit



Fig 20b. Switching Time Waveforms

DirectFET® Board Footprint, L8 (Large Size Can).
Please see DirectFET® application note AN-1035 for all details regarding the assembly of DirectFET®.
This includes all recommendations for stencil and substrate designs.





Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

DirectFET® Outline Dimension, L8 (Large Size Can).

Please see DirectFET® application note AN-1035 for all details regarding the assembly of DirectFET®. This includes all recommendations for stencil and substrate designs.



DIMENSIONS				
	METRIC		IMPERIAL	
CODE	MIN	MAX	MIN	MAX
A	9.05	9.15	0.356	0.360
B	6.85	7.10	0.270	0.280
C	5.90	6.00	0.232	0.236
D	0.55	0.65	0.022	0.026
E	0.58	0.62	0.023	0.024
F	1.18	1.22	0.046	0.048
G	0.98	1.02	0.039	0.040
H	0.73	0.77	0.029	0.030
J	0.38	0.42	0.015	0.017
K	1.35	1.45	0.053	0.057
L	2.55	2.65	0.100	0.104
L1	5.35	5.45	0.211	0.215
M	0.68	0.74	0.027	0.029
P	0.09	0.17	0.003	0.007
R	0.02	0.08	0.001	0.003

DirectFET® Part Marking



Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

DirectFET® Tape & Reel Dimension (Showing component orientation)



NOTE: Controlling dimensions in mm
Std reel quantity is 4000 parts. (ordered as AUIRF7769L2TR).

REEL DIMENSIONS				
STANDARD OPTION **(QTY 4000)**				
	METRIC		IMPERIAL	
CODE	MIN	MAX	MIN	MAX
A	330.00	N.C	12.992	N.C
B	20.20	N.C	0.795	N.C
C	12.80	13.20	0.504	0.520
D	1.50	N.C	0.059	N.C
E	99.00	100.00	3.900	3.940
F	N.C	22.40	N.C	0.880
G	16.40	18.40	0.650	0.720
H	15.90	19.40	0.630	0.760



NOTE: CONTROLLING DIMENSIONS IN MM

DIMENSIONS				
	METRIC		IMPERIAL	
CODE	MIN	MAX	MIN	MAX
A	11.90	12.10	4.69	0.476
B	3.90	4.10	0.154	0.161
C	15.90	16.30	0.623	0.642
D	7.40	7.60	0.291	0.299
E	7.20	7.40	0.283	0.291
F	9.90	10.10	0.390	0.398
G	1.50	N.C	0.059	N.C
H	1.50	1.60	0.059	0.063

Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

Qualification Information

Qualification Level		Automotive (per AEC-Q101)	
		Comments: This part number(s) passed Automotive qualification. Infineon's Industrial and Consumer qualification level is granted by extension of the higher Automotive level.	
Moisture Sensitivity Level		DFET2 Large Can	MSL1
ESD	Machine Model	Class M4 (+/- 800V)† AEC-Q101-002	
	Human Body Model	Class H3A (+/- 6000V)† AEC-Q101-001	
	Charged Device Model	N/A AEC-Q101-005	
RoHS Compliant		Yes	

† Highest passing voltage.

Revision History

Date	Comments
10/5/2015	• Updated datasheet with corporate template • Corrected ordering table on page 1. • Updated Tape and Reel option on page 10

Published by
Infineon Technologies AG
81726 München, Germany

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.