






- Note
1. 50 pieces per pack.
 2. () are reference dimensions.
 3. Please refer to the technical specification (ETAP-H1189-00) for the packing type.
 4. Refer to these manuals for handling this connector.
Cable assembly: ETAD-H0798-01
Mating and unmating operation: ETAD-H1025-00
 5. Screw size: M3
Recommended torque: 0.3 to 0.5 N·m
 6. There may be slight scratches or dents on the appearance, but this does not affect the function.
 7. UL (File No. E52653)
C-UL (File No. E52653)
TÜV (Certificate No. R9950703) authorization article



1	PBT	UL94V-0, BLACK		2	Cooper alloy	Surface : Gold plating 0.2μm MIN Base : Nickel plating 1μm MIN		
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
								
		APPROVED : S.J. OKAMURA		2025. 03. 28	DRAWING NO. EDC-406663-00-00			
		CHECKED : TT. OHSAKO		2025. 03. 28	PART NO. DF22BA-2EP-7. 92A-3PRT			
		DESIGNED : KT. NUMATA		2025. 03. 27	CODE NO. CL0680-1216-0-00			
HIROSE ELECTRIC CO., LTD.		DRAWN : KT. NUMATA		2025. 03. 27	0 11			