



**SCDN 3.81/28/90F 3.2SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Extra flat two-tier SCDN pin header for wave soldering.

- Two compact interfaces are used with the flat BCF 3.81 (PUSH IN) socket block.
- Available as 90° (recumbent).
- Connections on a single level, allowing access that is flush over the front board.
- Space for labelling and coding
- Packed in cardboard box.

Weidmüller's 3.81-mm-pitch (0.15 inch) plug-in connectors are compatible with the layouts of standard connectors and offer space for labelling and coding.

**General ordering data**

|              |                                                                                                                                                          |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, Flange, THT solder connection, 3.81 mm, Number of poles: 28, 90°, Solder pin length (l): 3.2 mm, tinned, orange, Box |
| Order No.    | <a href="#">1041080000</a>                                                                                                                               |
| Type         | SCDN 3.81/28/90F 3.2SN OR BX                                                                                                                             |
| GTIN (EAN)   | 4032248769926                                                                                                                                            |
| Qty.         | 20 pc(s).                                                                                                                                                |
| Product data | IEC: 320 V / 17.5 A<br>UL: 300 V / 10 A                                                                                                                  |
| Packaging    | Box                                                                                                                                                      |

Creation date June 16, 2025 6:06:44 PM CEST

## SCDN 3.81/28/90F 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Depth                    | 13.3 mm    | Depth (inches)  | 0.524 inch |
| Height                   | 18.4 mm    | Height (inches) | 0.724 inch |
| Height of lowest version | 15.2 mm    | Width           | 63.73 mm   |
| Width (inches)           | 2.509 inch | Net weight      | 7.4 g      |

## System specifications

|                                              |                                                  |                     |                                                    |
|----------------------------------------------|--------------------------------------------------|---------------------|----------------------------------------------------|
| Product family                               | OMNIMATE Signal - series BC/SC 3.81              |                     |                                                    |
| Type of connection                           | Board connection                                 |                     |                                                    |
| Mounting onto the PCB                        | THT solder connection                            |                     |                                                    |
| Pitch in mm (P)                              | 3.81 mm                                          |                     |                                                    |
| Pitch in inches (P)                          | 0.15 "                                           |                     |                                                    |
| Outgoing elbow                               | 90°                                              |                     |                                                    |
| Number of poles                              | 28                                               |                     |                                                    |
| Number of solder pins per pole               | 1                                                |                     |                                                    |
| Solder pin length (l)                        | 3.2 mm                                           |                     |                                                    |
| Solder pin length tolerance                  | +0,02 / -0.2 mm                                  |                     |                                                    |
| Solder pin dimensions                        | d = 1.0 mm, Octagonal                            |                     |                                                    |
| Solder pin dimensions = d tolerance          | 0 / -0,03 mm                                     |                     |                                                    |
| Solder eyelet hole diameter (D)              | 1.2 mm                                           |                     |                                                    |
| Solder eyelet hole diameter tolerance (D)    | + 0,1 mm                                         |                     |                                                    |
| L1 in mm                                     | 49.53 mm                                         |                     |                                                    |
| L1 in inches                                 | 1.95 "                                           |                     |                                                    |
| Number of rows                               | 2                                                |                     |                                                    |
| Pin series quantity                          | 2                                                |                     |                                                    |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe unplugged/ back-of-hand-safe plugged |                     |                                                    |
| Touch-safe protection acc. to DIN VDE 0470   | IP20 plugged/ IP10 unplugged                     |                     |                                                    |
| Volume resistance                            | ≤5 mΩ                                            |                     |                                                    |
| Can be coded                                 | Yes                                              |                     |                                                    |
| Tightening torque                            | Torque type                                      | Mounting screw, PCB |                                                    |
|                                              | Usage information                                | Tightening torque   | min. 0.1 Nm                                        |
|                                              |                                                  |                     | max. 0.15 Nm                                       |
|                                              |                                                  | Recommended screw   | Part number <a href="#">PTSC KA 2.2X4.5 WN1412</a> |

## Material data

|                                       |          |                                       |        |
|---------------------------------------|----------|---------------------------------------|--------|
| Insulating material                   | PA GF    | Colour                                | orange |
| Colour chart (similar)                | RAL 2000 | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 550    | UL 94 flammability rating             | V-0    |
| Contact material                      | Cu-alloy | Contact surface                       | tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C  |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 120 °C |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 120 °C |

**SCDN 3.81/28/90F 3.2SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 13.2 A                 | Rated current, min. number of poles (Tu=40°C)                         | 17 A             |
| Rated current, max. number of poles (Tu=40°C)                             | 12.2 A                 | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 76 A |

**Rated data acc. to CSA**

|                                   |       |                                   |       |
|-----------------------------------|-------|-----------------------------------|-------|
| Rated voltage (Use group B / CSA) | 300 V | Rated voltage (Use group D / CSA) | 300 V |
| Rated current (Use group B / CSA) | 11 A  | Rated current (Use group D / CSA) | 11 A  |

**Rated data acc. to UL 1059**

|                                       |       |                                       |       |
|---------------------------------------|-------|---------------------------------------|-------|
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group D / UL 1059) | 300 V |
| Rated current (Use group B / UL 1059) | 10 A  | Rated current (Use group D / UL 1059) | 10 A  |

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 275 mm |
| VPE width | 141 mm | VPE height | 29 mm  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002637    | ETIM 7.0    | EC002637    |
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1  | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |
| ECLASS 13.0 | 27-46-02-01 | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | cad4723c-c5fc-4802-be22-8cbcef126ab4 |

## SCDN 3.81/28/90F 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                        |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• P on drawing = pitch</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads



|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |



**SCDN 3.81/28/90F 3.2SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Drawings****Product image****Dimensional drawing**



NOTE:

n=NO OF POLES  
P=PITCH

KUNDENZEICHNUNG  
CUSTOMER DRAWING

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmüller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|    |         |           |
|----|---------|-----------|
| 32 | 57.15   | 2.250     |
| 30 | 53.34   | 2.100     |
| 28 | 49.53   | 1.950     |
| 26 | 45.72   | 1.800     |
| 24 | 41.91   | 1.650     |
| 22 | 38.10   | 1.500     |
| 20 | 34.29   | 1.350     |
| 18 | 30.48   | 1.200     |
| 16 | 26.67   | 1.050     |
| 14 | 22.86   | 0.900     |
| 12 | 19.05   | 0.750     |
| 10 | 15.24   | 0.600     |
| 8  | 11.43   | 0.450     |
| 6  | 7.62    | 0.300     |
| 4  | 3.81    | 0.150     |
| n  | L1 [mm] | L1 [inch] |

|                                      |  |                          |  |                         |            |  |
|--------------------------------------|--|--------------------------|--|-------------------------|------------|--|
| GENERAL TOLERANCE:<br>DIN ISO 2768-m |  | 78721/5<br>06.11.14 MA_J |  | 01                      | CAT.NO.: . |  |
| RoHS COMPLIANT                       |  | MAX. NRN./NOS.           |  | MODIFICATION            |            |  |
| DRAWN                                |  | DATE                     |  | NAME                    |            |  |
| RESPONSIBLE                          |  | 25.11.2014               |  | XU_S                    |            |  |
| CHECKED                              |  | 25.11.2014               |  | ZHOU_N                  |            |  |
| APPROVED                             |  | 25.11.2014               |  | XU_S                    |            |  |
| SCALE: 3/1                           |  | SUPERSEDES: .            |  | PRODUCT FILE: SCDN 3.81 |            |  |
| 7086                                 |  | 7086                     |  | 7086                    |            |  |

**Weidmüller**

**SCDN... 3.81/.../90...**  
THR-LOETANSCHLUSS STIFTSLEISTE  
THR SOLDER CONNECTION PIN HEADER

**C 46288**

DRAWING NO. SHEET 01 OF 03 SHEETS

ISSUE NO. 03

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.