








Sep.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

RECOMMENDED LAND PATTERN DIMENSION OF PCB

3 FLOATING RANGE



DRAWING FOR MATING: REFERENCES (FREE)



6	POLYESTER	CLEAR
5	POLYSTYRENE	CLEAR
4	BRASS	TIN PLATING 1μm MIN
3	COPPER ALLOY	CONTACT: GOLD PLATING 0.1μm MIN LEAD : GOLD PLATING 0.03μm MIN UNDER : NICKEL PLATING 1μm MIN

NO.	MATERIAL	FINISH . REMARKS
-----	----------	------------------


2	POLYAMIDE	BLACK, UL94V-0
1	POLYAMIDE	BLACK, UL94V-0
NO.	MATERIAL	FINISH . REMARKS
UNITS	mm	SCALE 2:1
COUNT	DESCRIPTION OF REVISIONS	DESIGNED
DATE	CHECKED	DATE
APPROVED : HS. OKAWA	16.01.16	DRAWING NO. EDC-336319-20-00
CHECKED : HT. YAMAGUCHI	16.01.16	PART NO. FX20-40P-0.5SV15(20)
DESIGNED : MT. ITANO	16.01.16	CODE NO. CL570-1001-0-20
DRAWN : MT. ITANO	16.01.16	

1	DATE	16.01.16
2	DATE	16.01.16
3	DATE	16.01.16
4	DATE	16.01.16
5	DATE	16.01.16
6	DATE	16.01.16
7	DATE	16.01.16
8	DATE	16.01.16




- NOTE 1 LEAD CO-PLANARITY IS 0.1mm MAX.
2 THIS IS PACKAGED IN EMBOSSED CARRIER TAPE. (260 PCS/RL)
3 FLOATING RANGE OF THIS CONNECTOR IS ±0.6mm MAX.
4 BLEMISH AND HIT MARK CAN BE OCCURED THROUGH OUT THE MANUFACTURING PROCESS WHICH DOESN' T AFFECT QUALITY LEVEL.
5 PLEASE NOTE THAT EXCESSIVE WRENCHING FORCE COULD DAMAGE THIS CONNECTOR.
PLEASE REFER TO THE GUIDELINE FOR DETAILED REGULATIONS OF THE MATING METHOD.

Sep.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

2 DRAWING FOR PACKING



REELING CONDITION FOR DELIVERY(FREE)



HRS

DRAWING NO.	EDC-336319-20-00
PART NO.	FX20-40P-0.5SV15(20)
CODE NO.	CL570-1001-0-20

2/2