




- NOTES 1 APPLICABLE CRIMP CONTACT: HR12-SC-242(CL112-0408-9)
APPLICABLE WIRE: AWG#26 TO #30 (COVERED WIRE MAX. OUTSIDE DIA. Ø1)
APPLICABLE CONTACT REMOVAL TOOL (EXTRACTION TOOL): HR12-SC-TP(CL150-0050-3)
2 APPLICABLE CRIMPING TOOL OF REF. NO. ⑦: HR10A-TC-02(CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING: Ø5.3
3 THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑤: 1.5 TO 2 N·m.
4 ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑥: 1.27 THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥: 0.3 TO 0.4 N·m.
THE TIP OF REF. NO. ⑥ SHALL BE FIXED TO THE CONCAVE PORTION WITH REF. NO. ⑦ CLAMPED TO THE CABLE.
① ⑤ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES TO PREVENT REF. NO. ① AND ⑥ FOR LOOSENING.
6 ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑤ TO REF. NO. ① IS SHOWN.
7 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.
① 8 THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0354-00.

4	STEEL	NICKEL PLATING		8	CHLOROPRENE RUBBER	(BLACK)				
3	BRASS	MATTE FINISH NICKEL PLATED		7	BRASS					
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0		6	STEEL	NICKEL PLATING M2.6X0.45X2				
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		5	BRASS	NICKEL PLATING				
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS				
UNITS mm		SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00017346		DESIGNED HT. ZENBA	CHECKED HY. KOBAYASHI	DATE 20240508	
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH			20070308		DRAWING NO.		EDC4-025177-73	
		CHECKED : EJ. KUNII			20070308		PART NO.		HR10A-7P-6SC(73)	
		DESIGNED : TO. HORII			20070308		CODE NO.		CL0110-0504-0-73	
		DRAWN : MK. SATO			20070308					