





- NOTES 1 APPLICABLE CRIMP CONTACT:
HR12-SC-212(CL112-0480-9)
APPLICABLE WIRE:AWG#26 TO #30
(COVERED WIRE MAX. OUTSIDE DIA.Ø1)
APPLICABLE CONTACT REMOVAL TOOL
(EXTRACTION TOOL):HR12-SC-TP(CL150-0052-9)
2 APPLICABLE CRIMPING TOOL OF REF.NO. ⑦:
HR10A-TC-02(CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING:Ø7.0
3 THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑤
: 2 TO 2.5 N·m.
4 ACROSS FLATS HEXAGON HEAD OF REF.NO. ⑥: 1.27
THE RECOMMENDED CLAMP TORQUE,
REF.NO. ⑥: 0.3 TO 0.4N·m.
THE TIP OF REF.NO. ⑥ SHALL BE FIXED TO
THE CONCAVE PORTION WITH REF.NO. ⑦ CLAMPED
TO THE CABLE.
5 LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
TO PREVENT REF.NO. ① AND ⑥ FOR LOOSENING.
6 ONE EXAMPLE OF THE ROTATION OF REF.NO. ⑤ TO
REF.NO. ① IS SHOWN.
7 THE CABLE PULL AND TWISTING STRENGTH AND
OTHER CHARACTERISTICS MAY DIFFER,
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.
8 THE ASSEMBLY THIS PRODUCT APPLIES TO
THE MANUAL ETAD-C0354-00.

4	STEEL	NICKEL PLATING		8	CHLOROPRENE RUBBER	(BLACK)		
3	BRASS	MATTE FINISH NICKEL PLATED		7	BRASS			
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0		6	STEEL	NICKEL PLATING M2.6X0.45X3		
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		5	BRASS	NICKEL PLATING		
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS		
UNITS mm		SCALE 2 : 1	 COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
		2 : 1	2	DIS-C-00017346		HT. ZENBA	HY. KOBAYASHI	20240508
 HIROSE ELECTRIC CO., LTD.		APPROVED :MO. SATOH		20070313	DRAWING NO.	EDC4-026324-73		
		CHECKED :EJ. KUNII		20070312	PART NO.	HR10A-10P-10SC(73)		
		DESIGNED :TO. HORII		20070309	CODE NO.	CL0110-0602-9-73		
		DRAWN :MK. SATO		20070309		 1/1		