





B Detail of mounting guide



Panel cutout
(t=0.7 to 2)




Note 1 The recommended clamp torque of Ref.No. ⑦ to be 2N · m.
Loctite 243, Henkel Japan or equivalent apply to prevent Ref.No. ⑦ from loosening.

△ CAD change

4	Phosphor bronze	Silver plating 2μm min.			
3	Polyamide	(Black) UL94V-0	7	Brass	Nickel plating
2	Stainless steel		6	Phosphor bronze	Nickel plating
1	Zinc alloy	Matte finish nickel plated	5	Phosphor bronze	Silver plating 2μm min.
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS
mm



SCALE
2:1

COUNT
2

DESCRIPTION OF REVISIONS
DIS-C-00018536

DESIGNED
HY. KISHI

CHECKED
HY. KOBAYASHI

DATE
2024. 10. 24

HRS

HIROSE
ELECTRIC
CO., LTD.

APPROVED : MO. SATOH 2005. 10. 20
CHECKED : EJ. KUNII 2005. 10. 20
DESIGNED : DS. MATSUNE 2005. 10. 19
DRAWN : DS. MATSUNE 2005. 10. 19

DRAWING NO. EDC-010387-71-71
PART NO. HR10A-10R-12S (71)
CODE NO. CL0110-0403-2-71

△ 1/1