



1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△										△									
△										△									
△										△									



- NOTES 1 APPLICABLE CRIMP CONTACT:HR10-PC-212(CL110-0514-3)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA. ϕ 1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):RP6-SC-TP(CL150-0039-0)
② THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ TO BE 1.5 N·m.
LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑤ FROM LOOSENING.

3	POLYBUTYLENE TEREPHTHALATE	(BLACK)	UL94V-0				
2	STAINLESS STEEL			5	BRASS	NICKEL PLATING	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		4	PHOSPHOR BRONZE	NICKEL PLATING	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	
CODE NO. (OLD) CL			DRAWN <i>M. Sato</i> <i>07.04.11</i>	DESIGNED <i>T. Hosoi</i> <i>07.04.11</i>	CHECKED <i>E. Kunita</i> <i>07.04.11</i>	APPROVED <i>M. Sato</i> <i>07.04.11</i>	RELEASED
		DRAWING NO. EDC4-042729-73		PART NO. HR10G-7R-6PC(73)			
SCALE 2 : 1		 HIROSE ELECTRIC CO., LTD.		CODE NO. CL110-1706-0-73			1/1
UNITS mm							

TO
R