





- 1 THE RECOMMENDED CLAMP TORQUE REF. NO. ⑥ : 5 TO 5.5 N · m.
- 2 THE RECOMMENDED CLAMP TORQUE REF. NO. ⑩ : 0.3 TO 0.4 N · m.
- 3 POSITIONAL RELATIONSHIP IN ROTATIONAL DIRECTION BETWEEN REF. NO. ① AND ⑥ SHOWS AN EXAMPLE.
- 4 LOCTITE 271, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ① AND NO. ⑩ FROM LOOSENING.
- 5 ROTATIONAL DIRECTION OF THE SOLDER CUP OF REF. NO. ② SHOWS AN EXAMPLE.
- 6 THIS PRODUCT TO BE USED WITH CABLECLAMP, JR25WCC-**(71).
** DESIGNATE DIAMETER OF APPLICABLE.
- 7 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER.
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

5	PHOSPHOR BRONZE	NICKEL PLATING	10	STAINLESS STEEL	
4	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	9	SILICONE RUBBER	(BLACK)
3	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	8	SILICONE RUBBER	(BLACK)
2	PHOSPHOR BRONZE	SILVER PLATING 2μm min.	7	BRASS	BLACK CHROME PLATING
1	ALUMINUM ALLOY	BLACK CHROME PLATING	6	BRASS	BLACK CHROME PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

 HIROSE ELECTRIC CO., LTD.		UNITS		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		mm						
		2 : 1						
		APPROVED :HY. KISHI	11. 03. 10	DRAWING NO. EDC3-112113-71				
		CHECKED :HY. KISHI	11. 03. 10	PART NO. JR25WP-3S(71)				
		DESIGNED :WR. AJIRO	11. 03. 10	CODE NO. CL114-2159-0-71				
		DRAWN :WR. AJIRO	11. 03. 10	 				