




- Notes
- 1 Rotation examples of ref. No. ① and ③ are shown.
 - 2 The recommended torque of ref. No. ⑧ : 2 to 3 N·m.
 - 3 The recommended torque of ref. No. ⑪ : 0.3 to 0.4 N·m.
 - 4 Bolting tool for ref. No. ⑪ : PB205/1.27 (CL150-0066-3)

			11	STEEL	NICKEL PLATING	THE WIDTH ACROSS OF A HEXAGON SOCKET : 1.27	
5	BRASS	MATTE FINISH NICKEL PLATING	10	BRASS	NICKEL PLATING		
4	PPS	(BLACK) UL94V-0	9	ZINC ALLOY	MATTE FINISH NICKEL PLATING		
3	PPS	(BLACK) UL94V-0	8	ZINC ALLOY	MATTE FINISH NICKEL PLATING		
2	COPPER ALLOY	SILVER PLATING 5μm min.	7	BRASS	NICKEL PLATING		
1	ZINC ALLOY	MATTE FINISH NICKEL PLATING	6	BERYLLIUM COPPER	NICKEL PLATING		
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00000559		DESIGNED KN. IKEHARA	CHECKED HY. KOBAYASHI
						DATE 15. 11. 02	
HRS HIROSE ELECTRIC CO., LTD.			APPROVED	HY. KOBAYASHI	15. 09. 10	DRAWING NO. EDC-112329-81-00	
			CHECKED	HY. KOBAYASHI	15. 09. 10	PART NO. RM12BPE-6S(81)	
			DESIGNED	KN. IKEHARA	15. 09. 10	CODE NO. CL109-0427-0-81	
			DRAWN	KN. IKEHARA	15. 09. 10		