




Notes 1

- △ Applicable crimp contact:
Contact No. 1 to 11
RP13A-SC-222/CL113-0151-0
(Applicable cable size : AWG#24 to #28.
Cable jacket outer diameter shall be $\phi 1.4$ mm or less.)
Contact No. 12,13
RP13A-SC-212/CL113-0150-8
(Applicable cable size : AWG#18 to #22.
Cable jacket outer diameter shall be $\phi 1.9$ mm or less.)
Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
Extraction tool : RP13A-SC-TP/CL150-0022-8
The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N · m.
To prevent loosening Ref No. ⑥ , use LOCTITE 243,
HENKEL JAPAN or equivalent.
5 Shall be disassembled when delivered.
△ 6 The cable pull and twisting strength and other
characteristics may differ, depending on the cable
structure. Please confirm before the use.

4	Brass								
3	Polycarbonate	(Black) UL94V-0		7	Polyvinylchloride	(Black)			
2	Polycarbonate	(Black) UL94V-0		6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4			
1	Polycarbonate	(Black) UL94V-0		5	Steel	Nickel plating			
NO.	MATERIAL	FINISH . REMARKS			NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 2 : 1		COUNT 4	DESCRIPTION OF REVISIONS DIS-C-00009807		DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20220214
HIROSE ELECTRIC CO., LTD.		APPROVED :MR. YOSHIDA			20050105	DRAWING NO. EDC-009947-71-71			
		CHECKED :MO. SATOH			20050105	PART NO. RP13A-12PD-13SC(71)			
		DESIGNED :YH. YAMADA			20050105	CODE NO. CL0113-0186-5-71			
		DRAWN :YH. YAMADA			20050105				