




- Notes
- ① 1 Applicable crimp contact:
RP19-SC-222/CL113-0266-2 (Applicable cable size : AWG#24 to #28.
Cable jacket outer diameter shall be $\phi 1.15\text{mm}$ or less.)
 - ① 2 Applicable cable crimping tool : RP13A-TC-01/CL150-0070-0
 - ③ Extraction tool : RP6-SC-TP/CL150-0039-0
 - ① ④ The tightening torque of Ref No. ⑥ : 0.15 to 0.2 N·m.
To prevent loosening Ref No. ⑥ , use LOCTITE 243, HENKEL JAPAN or equivalent.
 - 5 Shall be disassembled when delivered.
 - 6 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure, please confirm before the use.

4	Brass			7	Polyvinylchloride	(Black)
3	Polycarbonate	(Black)	UL94V-0	6	Brass	Black chromete treatment (Trivalent chromium) JIS B 1111 M2X0.4X4
2	Polycarbonate	(Black)	UL94V-0	5	Steel	Nickel plating
1	Polycarbonate	(Black)	UL94V-0			
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT ① 4	DESCRIPTION OF REVISIONS DIS-C-00009810		DESIGNED TY. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : EJ. KUNII		DRAWING NO. EDC-021588-71-00		
		CHECKED : EJ. KUNII		PART NO. RP13A-12PG-20SC(71)		
		DESIGNED : MM. ISHII		CODE NO. CL0113-0210-8-71		
		DRAWN : MM. ISHII				