




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI9805	04DEC2018	I.G	S.B
	A	REVISED PER PCN E-18-018867	04DEC2018	J.A	D.M
	AI	REVISED PER PCN E-19-007592	09JAN2020	CO	IG



SECTION A-A



3D VIEW

3. PANEL NUT MOUNTING TORQUE:
- SIZE 24
361 ± 60.2 in-lbf [40.8 ± 6.8 Nm]
- SIZE 32
1625 ± 120.4 in-lbf [183.6 ± 13.6 Nm]


2. PLATING: CLEAR TRIVALENT CHROMATE CONVERSION COATING (ROHS COMPLIANT)

1. MATERIAL: ALUMINUM

NOTES:

TE PART NUMBER	DEUTSCH PART NUMBER	REV
8NI522-32	8NI522-32	C
8NI536-24	8NI536-24	

PART NUMBER	SIZE	A [mm]	B [mm]	D THREAD
8NI536-24 2334627-1	24	1.812 [46.02]	.160 [4.06]	1.625-18UNEF-2B
8NI522-32 2334720-1	32	2.495 [63.37]	.265 [6.73]	2.250-16UN-2B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN I. GRANTCHAROVA 3/24/08	 TE Connectivity		
DIMENSIONS: in [mm]		CHK D. WHITACRE 12/23/08			
		APVD S. BEARD 06/29/09	NAME NUT, PANEL BAYONET COUPLING C.E. SERIES SIZE 24 & 32 -		
		PRODUCT SPEC -			
MATERIAL 		APPLICATION SPEC -	SIZE A3		
		FINISH 			
		WEIGHT -	CAGE CODE 4AFU8		
		CUSTOMER DRAWING	DRAWING NO 8NI536-24/8NI522-32		
			RESTRICTED TO -		
			SCALE 1:1		
			SHEET 1 OF 1		
			REV AI		