

Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2209545-1
94P, MQS CB, REC HSG, ASSY, SEALED




TE Part # CAT-M8793-T273
MQS, RECEPTACLE AND TAB



TE Part # 1241609-6
SOCKET CONTACT0,63X1,5 AG , LP



TE Part # 2209544-9
60P, PLUG ASSY, NORMAL CODING



TE Part # 1452157-1
MQS1,5 SOCKET CONTACT



TE Part # 2209544-1
60P, MQS CB, REC HSG, ASSY, SEALED



TE Part # 2208277-3
60POS MQS REC SEALED



TE Part # 6-968220-6
MQS RECEPTACLE CONTACT

Customers Also Bought



TE Part #244855-E
SMCQ 26 M AB VV 8-03 CL * H007 137 E005



TE Part #TAD14545101-020
M12D4-MS-FS-PUR-22SH-TYPE C
GREEN-2.0M



TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #1-1355132-2
SHIELD, 94POSN., RECEPTACLE HO



TE Part #7-1393114-7
KUHP-11D51-12-KU



TE Part #1-1414552-0
V23136A1001X057-EV-CBOX



TE Part #7-2176089-0
RP 1J 0.166W 60K4 0.1% 25PPM 1K RL



TE Part #539951-2
ERGO DIE MCP 2,8K



Documents

Product Drawings

EXTRACTION TOOL

English

Datasheets & Catalog Pages

CRIMPING TERMINALS

English

CRIMPING WHERE FORM MEETS FUNCTION

English