




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 642.4 – 2583 CMA

Stud Size: 1/4

Features

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	1/4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.53 g
----------------	--------

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	None



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.059 in
Wire Size	642.4 – 2583 CMA
Stud Diameter	6.3 mm [.24 in]
Tongue Thickness	.76 mm [.03 in]
Product Length	24.89 mm [.98 in]
Barrel Inside Diameter	.89 mm, 1.77 mm [.035 in] [.07 in]
Compatible Insulation Diameter (Max)	.3 mm [.118 in]
Compatible Insulation Diameter Range	1.5 – 3 mm [.059 – .118 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150318-2
OCEAN_2.0_Applicator-E-110F1400-REA

KIT
REPRESENTATION ONLY

TE Part # 7-2150318-7
OCEAN_2.0_SPARE_PART_KIT-110F1400

TE Part # 160548-2
RING TONGUE 22-20 AWG .0120 X .290 TPBR

Customers Also Bought

TE Part #ANT-GNSSCP-TH18L1
Antenna GNSS L1 18x18 THM

TE Part #42938-2
RING 16-14 AWG TPBR

TE Part #63850-1
187 FASTON REC 20-16 AWG NPST

TE Part #280756-2
FF 375 REC 3-6MM2 TPBR

TE Part #626038-2
RING TONGUE 4-6 MM2 0.79 X 16.18 TPBR

TE Part #1376360-1
025/090 26P PLUG ASSY

TE Part #CAT-H3399-CH8172
Heavy Duty Sealed Connector Series Housings

TE Part #2108784-2
PCB ANTENNA, SMD, 698-6000MHz



Documents

Product Drawings

RING TONGUE 1/4 22-16 AWG TPBR

French

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_140731-2_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_140731-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_140731-2_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

114-2084

English

Agency Approvals

Agency Approval Document

English