



Microdot

TE Internal #: 1532216-2
100 Position D-Shaped Connector, Plug, Cable-to-Board, Panel Mount, 1.27 mm [.05 in] Centerline, Wire & Cable, Signal, -55 – 125 °C [-67 – 257 °F]

[View on TE.com >](#)

Connectors > D-Shaped Connectors



Number of Positions: 100
Connector & Housing Type: Plug
Connector System: Cable-to-Board
Connector Mounting Type: Panel Mount
Centerline (Pitch): 1.27 mm [.05 in]

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	100
---------------------	-----

Contact Features

Contact Current Rating (Max)	3 A
Contact Options	Installed

Termination Features

Termination Method to Wire & Cable	Solder Cup
------------------------------------	------------

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	1.27 mm[.05 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Cd (100% in 10563731072) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #NB-PTCO-126
[Pt1000, 2.0x5.0, Class B, PTFD102B1G0](#)



TE Part #024070-E
[STVBUG E 160 CSI 172 9999 * J 4 24070 FE](#)



TE Part #CJ8362-000
[S200-4-W2-22-9](#)



TE Part #F99802-000
[S200-3-W1-22-9](#)



TE Part #204520-2
RECEPT ASSY,78 POSN,AMPLIMITE




TE Part #204521-2
AMPLIMITE,ASY,PLUG,STD,90,5




TE Part #204523-2
AMPLIMITE,ASY,PLUG,STD,90,6



TE Part #1532203-1
M83513/02-CN, MCKS-N1-B-21SS



TE Part #1-1903127-1
DYNAMIC 1100D TAB HSG 22P F/H



TE Part #533311-2
40 POSN ECON II HDR ASSY

Documents

Product Drawings

M83513/01-HC, MCKS-C2-B-100PS

English

CAD Files

Customer View Model

ENG_CVM_CVM_1532216-2_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1532216-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1532216-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.