

T300-RIBBON-WH-4HT

✓ ACTIVE

4HT


TE Internal #: 154739-000

Resin Printer Ribbon, 984 ft, [300 m] Length, 100 mm [3.9 in] Width, 4HT

[View on TE.com >](#)



Identification & Labeling > Printer Ribbons



Printer Ink Type: **Resin**
Primary Product Color: **White**
Printer Ribbon Length: **300 m [984 ft]**
Product Width: **100 mm [3.9 in]**

Features

Product Type Features

Printer Ink Type	Resin
------------------	-------

Configuration Features

Ribbon Configuration	Ink Side Out (Reverse Wound)
Ribbon Type	Thermal Transfer

Body Features

Primary Product Color	White
-----------------------	-------

Dimensions

Printer Ribbon Length	300 m[984 ft]
Product Width	100 mm[3.9 in]

Operation/Application

Compatible Printers	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T3437-H85999A
HT-SCE High Temperature Sleeves



TE Part # CB4071-000
HT-SCE-1K-1-1/2-2.0-0

Also in the Series | 4HT



Printer Ribbons(2)

Customers Also Bought



TE Part #720633-000
301A511-51/164-0

TE Part #CAT-R21-567014
Low Profile HS Boots: Blow Molded,
Slim Line, Lipped, Straight

TE Part #EL7358-000
HT-CT-50M-3/8-OUT-9

TE Part #216787-000
SO96-3-55-22-90

TE Part #NB15794001
RNF-150-3/8-0-SP

TE Part #0660-206-1282
CONT PIN

TE Part #CAT-R21-731072
Bulbous Heat Shrink Boots: Lipped,
Straight

TE Part #245783N001
RNF-100-3/16-BK-SP-CS5004

Documents

Product Drawings

T300-RIBBON-WH-4HT

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English