




Automotive Parts > Automotive Connectors > Automotive Headers > Signal Header



PCB Mount Orientation: **Vertical**
Termination Method to PCB: **Through Hole - Screw**
Sealable: **No**
Centerline (Pitch): **2.2 mm, 4 mm** [.087 in, .157 in]
Connector System: **Wire-to-Board**

[All Signal Header \(240\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
Mixed & Hybrid Header	Yes
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	20
Number of Sections	1
PCB Mount Orientation	Vertical
Number of Positions	26
Number of Rows	2



Electrical Characteristics

Operating Voltage	12 VDC
Voltage Rating (Max)	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Mating Tab Width	.64 mm, 2.3 mm [.025 in][.09 in]
Mating Tab Thickness	.64 mm [.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Screw
---------------------------	----------------------

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	Without
Mounting Holes	With
Mating Alignment	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.2 mm, 4 mm [.087 in][.157 in]
--------------------	---------------------------------

Dimensions

Connector Width	15.5 mm [.61 in]
PCB Thickness (Recommended)	1.2 – 1.6 mm [.047 – .063 in]
Profile Height from PCB	25.9 mm [1.02 in]
Connector Length	42.5 mm [1.673 in]

Usage Conditions

Operating Temperature (Max)	105 °C [221 °F]
Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]



Operation/Application

Shielded	No
Circuit Application	Power & Signal

Packaging Features

Packaging Method	Tube
------------------	------

Other

Interface Number	1376360, 1674932
------------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING

Also in the Series | 0.64/025 Connector System



Automotive Connector Locks &
Position Assurance(1)



Automotive Housings(174)



Automotive Seals & Cavity Plugs(2)



Automotive Signal & Power Connector
Housings(174)


Customers Also Bought




TE Part #214013-E
SRCA 1,27 6 M 1 SMD 137 E1 094 *
GURT *




TE Part #100616-2
8/8 MOD.JACK ASSY TE SHIELDED



TE Part #177766-1
ELECTRO TAP ASSY



TE Part #1376360-1
025/090 26P PLUG ASSY



TE Part #1827855-1
0.50 SERIES CONNECTER
RECEPTACLE CONTACT



TE Part #1903608-4
0.50 SERIES CONN 12POS PLUG
HOUSING ASSY



TE Part #CAT-A12-CH8172
0.50 CONNECTOR SYSTEM,
CONNECTOR HOUSING



TE Part #1-1903607-3
1.5 SERIES CONNECTOR 4POS LOCK
HOUSING

Documents

Product Drawings

CAD Files

Customer View Model

ENG_CVM_CVM_1565371-3_E.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1565371-3_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1565371-3_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese

Instruction Sheets

025/090II I/O Connector

Japanese

Instruction Sheet (non U.S.)

Japanese

025/090II I/O Connector

Japanese

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

English