



CII

TE Internal #: 1617784-6

General Purpose Power Relay, DC, Polarized, Monostable, 2 Form C DPDT-CO, 10 A Contact Rating, 6 VDC Coil Voltage, Board Mount, Hermetically Sealed

[View on TE.com >](#)

Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Current Type: **DC**

Contact Current Rating: **10 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay
------------------------	-----------------------------

Configuration Features

Coil Special Features	Coil Suppression Diode
Relay Options	Back EMF Suppression
Contact Arrangement	2 Form C DPDT-CO

Electrical Characteristics

Coil Resistance	20 Ω
Contact Switching Voltage (Max)	115 VAC, 200 VAC
Contact Current Rating	10 A
Coil Voltage Rating	6 VDC

Body Features

Enclosure Type	Hermetically Sealed
----------------	---------------------

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Tin-Lead

Termination Features

Main Termination & Connection Type	Solder Pins
------------------------------------	-------------



Coil Termination & Connection Type	Solder Pins
Mechanical Attachment	
Product Mount Type	Board Mount
Usage Conditions	
Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
Environmental Ambient Temperature (Max)	125 °C[257 °F]
Operation/Application	
Vibration Resistance	30G's, 10 – 3000Hz
Shock Resistance	200G's, 6ms
Coil Magnetic System	Polarized, Monostable
Current Type	DC
Other	
Contact Current Class	>5 – ≤10 A

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An




Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 5-1617785-7
[FCA-410-1521L=M83536/15-021L](#)


Customers Also Bought



TE Part #9-1589788-2
[STM009PC2DM048Q = Wdualobe](#)




TE Part #8-1617349-0
[3SBM1089A2=M39016/36-006M](#)




TE Part #3-1617515-0
[3SBC1793A2=M39016/13-101M](#)




TE Part #5-1617800-8
[FCAC-150-KY4=50 AMP MID RANGE RELAY](#)



TE Part #65053-234
[ELEC MODULE](#)



TE Part #070539-000
[TXR21AB90-1608AI](#)



TE Part #1051900-1
[2032 8007 92](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1617784-6_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617784-6_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1617784-6_A.3d_stp.zip](#)

1617784-6

General Purpose Power Relay, DC, Polarized, Monostable, 2 Form C DPDT-CO, 10 A
Contact Rating, 6 VDC Coil Voltage, Board Mount, Hermetically Sealed



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec5_FCA-210

English