

**IE-C5DS4VG0020MCSA24-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |                                                                                                                                       |
|------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Version    | System cable, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 2 m |
| Order No.  | <a href="#">1121150020</a>                                                                                                            |
| Type       | IE-C5DS4VG0020MCSA24-X                                                                                                                |
| GTIN (EAN) | 4050118676365                                                                                                                         |
| Qty.       | 1 pc(s).                                                                                                                              |

**IE-C5DS4VG0020MCSA24-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Length     | 2 m      | Length (inches) | 78.74 inch |
| Net weight | 142.56 g |                 |            |

**Temperatures**

|                          |                |                       |                |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature      | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C |                       |                |

**Cable specific standards**

|                                |                                                                        |                              |                          |
|--------------------------------|------------------------------------------------------------------------|------------------------------|--------------------------|
| Standard, additional standards | UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8 | Standard, assembly           | UL-Style 21694           |
| Standard, insulating material  | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)                      | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material        | DIN EN 13602 Cu-ETP-A                                                  |                              |                          |

**Cable structure**

|                              |                                                         |                                       |                                            |
|------------------------------|---------------------------------------------------------|---------------------------------------|--------------------------------------------|
| Arrangement of wire cores    | Star-quad                                               | Colour sequence or wires - wire pairs | white, yellow, blue, orange                |
| Complete shielding           | Aluminium foil, Shielding braid made from copper wiring | Cross-section                         | 4*AWG 22/7 - 0.32 mm <sup>2</sup>          |
| Diameter of inner sheathing  | 4.05 mm                                                 | Filler                                | As central element                         |
| Insulation                   | PE                                                      | Insulation cross-section              | 1.5 mm                                     |
| Material sheath              | PVC                                                     | Number of wires                       | 4                                          |
| Overlap of shielding braid   | 85 %                                                    | Sheath diameter, max.                 | 6.7 mm                                     |
| Sheath diameter, min.        | 6.3 mm                                                  | Sheathing colour                      | green (RAL 6018)                           |
| Sheathing material thickness | 0.9 mm                                                  | Shielding                             | SF/UTP                                     |
| Shielding braid thickness    | 0.13 mm                                                 | Standard designations                 | 2YY(ST)CY<br>2x2x0.75/1.5-100 LI VZN<br>GN |
| Strands                      | 7                                                       | Wire material                         | Stranded tin-plated copper wire            |

**Electrical properties of cable**

|                                |                                             |                               |                     |
|--------------------------------|---------------------------------------------|-------------------------------|---------------------|
| Category                       | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Characteristic impedance      | 100 ± 5 Ω at 100MHz |
| Loop resistance                | 120 Ω/km                                    | Operating voltage (UL rating) | 600 V               |
| Operating voltage, UL          | 600 V                                       | Signal propagation time       | 5.3 ns/m            |
| Test voltage: wire-wire-shield | 2000 V <sub>eff</sub> , 50 Hz, 1 min        | Transfer impedance            | 20 mΩ/m at 10 MHz   |

**Mechanical and material properties of cable**

|                                |                                          |                                 |                      |
|--------------------------------|------------------------------------------|---------------------------------|----------------------|
| Abrasion resistance            | good                                     | Halogen                         | Yes                  |
| Min. bending radius, once only | 3.5 *diameter                            | Min. bending radius, repetitive | 7.5 x cable diameter |
| Resistance to spread of flame  | in accordance with IEC 60332-1 / UL 1685 |                                 |                      |

**IE-C5DS4VG0020MCSA24-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 9.0  | 27-06-03-08 |
| ECLASS 9.1  | 27-06-03-08 | ECLASS 10.0 | 27-06-03-08 |
| ECLASS 11.0 | 27-06-03-08 | ECLASS 12.0 | 27-06-03-08 |
| ECLASS 13.0 | 27-06-03-08 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 67cf1078-beca-4687-860b-dc475a6ec24a |

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|