




Automotive Parts > Automotive Connectors > Automotive Headers > SUPERSEAL 1.0 Connector Headers



Sealable: No

Connector System: Wire-to-Board

Number of Positions: 34

Number of Rows: 4

Connector & Contact Terminates To: Printed Circuit Board

[All SUPERSEAL 1.0 Connector Headers \(39\)](#)

Features

Product Type Features

Header Type	Unshrouded
Connector Product Type	Connector Assembly
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	34
Number of Rows	4

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Pin
--------------	-----

Mechanical Attachment



Mating Alignment	With
------------------	------

Industry Standards

UL Flammability Rating	12mm Flame Test per Standard UL 746C
------------------------	--------------------------------------

Packaging Features

Packaging Method	Carton Box With Tray
------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series

SUPERSEAL 1.0mm



Customers Also Bought





Documents

Product Drawings

34POS,PIN DIA 1.0,HEADER ASSY,180 DEG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2303344-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2303344-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2303344-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English