




TE Internal #: 2319023-2

Others, Mini ATM Fuse, 1 Fuses (Maximum), 1 Fuses (Minimum),  
Micro Relay, 1 Relays (Maximum), 1 Relays (Minimum), 8 Position,  
Other Hard Wired Boxes

[View on TE.com >](#)

Automotive Parts > Automotive Power Distribution Boxes > Other Hard Wired Boxes



Component Type: Others

Fuse Type: Mini ATM Fuse

Number of Fuses (Maximum): 1

Number of Fuses (Minimum): 1

Compatible With Relay Type: Micro Relay

Features

Product Type Features

Component Type	Others
Fuse Type	Mini ATM Fuse
Compatible With Relay Type	Micro Relay
Sealable	Yes
Primary Locking Feature	Locking Lance, On the Terminal

Configuration Features

Number of Fuses (Maximum)	1
Number of Fuses (Minimum)	1
Number of Relays (Maximum)	1
Number of Relays (Minimum)	1
Number of Positions	8

Electrical Characteristics

Nominal Voltage Architecture	24 V
------------------------------	------

Body Features

--	--



Secondary Locking	No
-------------------	----

Contact Features

Contact Current Rating (Max)	30 A
------------------------------	------

Housing Features

Centerline (Pitch)	8.1 mm[.319 in]
--------------------	-----------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 30702560846) Decamethylcyclopentasiloxane (D5) (.5% in 30702560846) Octamethylcyclotetrasiloxane (D4) (.5% in 30702560846) <b>Article Safe Usage Statements:</b> Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products




will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # CAT-AM705-T273  
AMP MCP, RECEPTACLE AND TAB




TE Part # 1443998-1  
FUSE PULLER




TE Part # CAT-D487-M8649  
DEUTSCH DT Mounting Clips




TE Part # 828905-1  
SINGLE-WIRE-SEAL(5MM HOLE)




TE Part # 828904-1  
SINGLE WIRE SEAL FOR J.P.T.CON




TE Part # CAT-AM7801-M8649  
AMPSEAL 16 Connectors Mounting Clips



TE Part # 2319021-2  
REC CONN CVR,8POS,AMP MCP 2.8, FRB



TE Part # 1-1579007-2  
EXTRACTION TOOL



TE Part # 828922-1  
2,5MM CAVITY PLUG FOR 5,4MM DI

Customers Also Bought



TE Part #1027-003-1200  
CLIP, SS, 11MM HOLE, ST



TE Part #DTM04-3P-E003  
REC, 3P, GRY, N, CAP



TE Part #DT04-3P-CE09  
REC, 3P, BLK, E, XCAP



TE Part #HD10-9-1939PE-B022  
REC, 9P, BLK, E, PANEL, J1939, TYPE 1






TE Part #34126  
TERMINAL,SOLIS R 16-14 3/8



TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM,  
CONNECTOR HOUSING



TE Part #1-968317-3  
MQS ABDECKKAPPE 24P



TE Part #1-968318-1  
12POS MQS REC COD A



TE Part #1-968876-1  
AMP MCP 2.8, CONTACT SWS (LP)

Documents

Product Drawings

8POS,AMP MCP 2.8,REC HSG ASSY,SLD

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2319023-2\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2319023-2\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2319023-2\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Fuse and Relay Enclosures

English

Product Specifications

Application Specification

English