



Application Tooling > Hand Crimping Tools



Die Sets Type: **Removable/Interchangeable**

TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **Die Assembly**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Die Sets Type	Removable/Interchangeable
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1355328-1
2POS,AMP MCP 9.5,REC HSG ASSY, SLD




TE Part # 539783-8
DIE MCP 9,5 6MM EDS




TE Part # 539783-9
DIE MCP9,5 10MM EDS



TE Part # 539793-7
CRIMP DIE SET HV 35 SQMM SHIELDED BRAID




TE Part # 539783-6
DIE MCP 9,5 10MM



TE Part # 539783-5
DIE MCP 9,5 6MM



TE Part # 1-929150-1
AMP MCP9.5,CONTACT,(LP)







TE Part # 1-528040-1
DIE SET W. LOCATOR F. HV SHIEL



TE Part # 1719832-2
8MM HV,ASSY

Customers Also Bought



 TE Part #182645-1 13-9 CPC PLUG	 TE Part #1-539783-0 DIE MCP9,5 16MM EDS	 TE Part #1-917484-2 DYNAMIC D-3 REC CONT. 2L AU 0.38	 TE Part #1355437-3 MCP9,5 EINZELDICHTG
 TE Part #1718348-1 MCON 1.2 CB TAB STC SN	 TE Part #4-2176238-4 CPF A 0805 5K1 0.1% 25PPM 5K RL	 TE Part #2-2176612-9 EP 3W (SS) 15R 5%	 TE Part #1-480435-0 FASTON 187 REC HSG NYLON NAT
 TE Part #920-359-002 DVB 4779 FL	 TE Part #955-181-003 CGNW 702659 SF S/FME/3.0		

Documents

Product Drawings
HZ FUER HOCHSTROMKO
German

Datasheets & Catalog Pages
Bottoming Dies
English