



PVF

TE Internal #: C68103-000

White, Self-Laminating, Die-Cut, Permanent Pressure Sensitive Acrylic Adhesive, 48.3 mm [1.9 in] Width, 151 mm [5.94 in] Height, PVF, Standard Labels

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > Self Laminating PVF Labels



Label Type: **Self-Laminating**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Pressure Sensitive Acrylic Adhesive**

Product Width: **48.3 mm [1.9 in]**

Length of Label Roll: **79.73 m [261.58 ft]**

[All Self Laminating PVF Labels \(12\)](#)

Features

Product Type Features

Printable Label Height	38.1 mm[1.5 in]
Label Type	Self-Laminating

Body Features

Primary Product Color	White
Primary Product Material	Polyvinyl Fluoride (PVF)

Dimensions

Product Width	48.3 mm[1.9 in]
Product Height	151 mm[5.94 in]
Compatible Cable Diameter Range	12.1 – 36 mm[.477 – 1.416 in]

Usage Conditions

Operating Temperature Range	-40 – 107 °C[-40 – 225 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	2
Label Style	Die-Cut
Length of Label Roll	79.73 m[261.58 ft]



Label Thickness	51 Micron
-----------------	-----------

Packaging Features

Packaging Method	Roll
Packaging Quantity	1000

Other

Label Adhesive Type	Permanent Pressure Sensitive Acrylic Adhesive
---------------------	---

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

PVF190594WE1

White, Self-Laminating, Die-Cut, Permanent Pressure Sensitive Acrylic Adhesive, 48.3 mm [1.9 in] Width, 151 mm [5.94 in] Height, PVF, Standard Labels





TE Part # 1-2186502-1
[T3224-PRINTER](#)



TE Part # 1-2186503-1
[T3224-SWARE-PRINTER](#)



TE Part # 1-2186500-1
[T3212-PRINTER](#)



TE Part # 1-2186501-1
[T3212-SWARE-PRINTER](#)

Also in the Series | [PVF](#)



[Standard Labels\(12\)](#)

Customers Also Bought



TE Part #2-322796-1
[STRATO R 22-16COMM 22-18MIL 4](#)



TE Part #1546670-4
[4P .437" DR BARRIER,W/BND SCR](#)

Documents

Product Drawings

[PVF190594WE1](#)

English

Datasheets & Catalog Pages

[PVF Technical Datasheet](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English

Product Specifications

[IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX](#)

English