



Switches > Toggle Switches > Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever



Configuration (Pole-Throw): **Single Pole - Double Throw**

Operating Function: **On Off On**

Number of Positions: **3**

Contact Current Rating: **20 A**

Operating Voltage: **28 VDC**

[All Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever \(38\)](#)

Features

Product Type Features

Sealed Device	Yes
Toggle Style	Lever
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On Off On
Number of Positions	3

Electrical Characteristics

Contact Current Rating	20 A
Operating Voltage	115 VAC

Body Features

Sealing Method	Strippable Transparent Protective Seal
----------------	--



Product Orientation	Horizontal
Bushing Style	Threaded
Bushing Thread Size	M12 x .75

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Silver Tin Oxide

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # K2001910
Toggle Switch 08-4-1-13 D



TE Part # K1018509
Dichtscheibe 08-0-0-50



TE Part # CAT-AL8-KSTS081
Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever



TE Part # K1131164
Toggle Switch 09-2-1-17 926



TE Part # CAT-AL8-KSTS091
Toggle Switch 1-Pole, Sealed, Lever, Toggle, Metal Lever



TE Part # K1009382
Switch guard 08-0-0-01 902



TE Part # K1125121
Switch guard 08-0-0-01 915



TE Part # K1131165
Toggle Switch 09-4-1-17 926



TE Part # K2001914
Toggle Switch 08-4-1-14 F



TE Part # K1021326
Toggle Switch 09-2-1-13 D



TE Part # CAT-AL8-KSTS071
Toggle Switch 1-Pole, Sealed, Lever, Toggle



TE Part # CAT-AL8-KSTS072
Toggle Switch 2-Pole, Sealed, Lever, Toggle



TE Part # K1150112
Toggle Switch 07-3-3-99 916



TE Part # K1041435
Switch guard 08-0-0-04 905



TE Part # K1145129
Switch guard 07-0-0-01 905




TE Part # K1040743
Toggle Switch 08-4-1-23 A



TE Part # K1150879
Switch guard 08-0-0-01 with NATO-No



TE Part # K1158447
Toggle Switch 07-1-2-13 931 Set Conti.



TE Part # K1139243
Bellow compl. FMQ 08-80-666



TE Part # K1002958
Toggle Switch 08-4-1-26 A


Also in the Series | **KISSLING Series 08**



Other Automotive Connector Accessories(1)



Switch Seals & Accessories(18)



Toggle Switches(125)

Customers Also Bought



TE Part #K1142490
Push button switch TS-211-SW11



TE Part #K1002924
Toggle Switch 08-2-1-14



TE Part #K1140735
Limit switch G12-212-D



TE Part #878184-000
222K142-12-0



TE Part #CAT-AL8-KSTS081
Toggle Switch 1-Pole, Sealed, Lever, Toggle, Plastic Lever



TE Part #K1133206
Toggle Switch 07-4-1-23 A



TE Part #K1160369
Relay 26-07-51-909



TE Part #927777-3
JUNIOR POWER TIMER CONTACT

Documents

Product Drawings

Toggle Switch 08-1-1-15

German

Toggle Switch 08-1-1-15

English

Toggle Switch 08-1-1-15

German

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_08-1-1-15_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_08-1-1-15_1.3d_igs.zip

English

08-1-1-15

20 A Toggle Switch, Single Pole - Double Throw Configuration (Pole-Throw), On Off On, 3 Position, 28 VDC, 115 VAC, Panel Mount, KISSLING Series 08



Customer View Model

[ENG_CVM_CVM_08-1-1-15_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KISSLING TOGGLE SWITCH Series 08](#)

English