


Captive Screw Type 1 10-24 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX

Captive Screws - 10-24 Thread

FCXXXX	Length (L)	H.D. +.015 / -.000	S.L. +.010 / -.010	D. +.010 / -.000
FC0138	5/8	7/16	1/4	1/16
FC0139	11/16	7/16	5/16	1/16
FC0140	3/4	7/16	3/8	1/16
FC0141	13/16	7/16	7/16	1/16
FC0142	7/8	7/16	1/2	1/16
FC0143	15/16	7/16	9/16	1/16
FC0144	1	7/16	5/8	1/16
FC0145	1-1/16	7/16	11/16	1/16
FC0146	1-1/8	7/16	3/4	1/16
FC0147	1-3/16	7/16	13/16	1/16
FC0148	1-1/4	7/16	7/8	1/16
FC0149	1-5/16	7/16	15/16	1/16
FC0150	1-3/8	7/16	1	1/16
FC0151	1-7/16	7/16	1-1/16	1/16
FC0152	1-1/2	7/16	1-1/8	1/16
FC0153	1-9/16	7/16	1-3/16	1/16
FC0154	1-5/8	7/16	1-1/4	1/16
FC0155	1-11/16	7/16	1-5/16	1/16
FC0156	1-3/4	7/16	1-3/8	1/16
FC0157	1-13/16	7/16	1-7/16	1/16
FC0158	1-7/8	7/16	1-1/2	1/16
FC0159	1-15/16	7/16	1-9/16	1/16
FC0160	2	7/16	1-5/8	1/16

Material

Material Code (XX)
B Brass
S Steel
SS Stainless Steel

Compatible Finish (XX)

Compatible Finish (XX)
B, S, SS 0 - Plain
B, S 5 - Nickel Plate (QQ-N-290)
B, S 12 - Zinc Clear (ASTM-B-633)
B, S 16 - Electro Tin (MIL-T-10727 TYPE 1)
SS 20 - Passivation (MIL-F-14072D)
B, S, SS 26 - Black Oxide
B, S 28 - Zinc Yellow (ASTM-B-633)

Tolerances

Unless otherwise Specified

.xxx +/- .005

.xx +/- .010

Angular +/- 1 Degree

Linear +/- .005

Break all sharp edges

Source Control Drawing:
To be produced by
Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.