

IE-C5DS4VG0065A20A20-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 6.5 m
Order No.	1191010065
Type	IE-C5DS4VG0065A20A20-E
GTIN (EAN)	4050118413649
Qty.	1 pc(s).

IE-C5DS4VG0065A20A20-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	6.5 m	Length (inches)	255.906 inch
Net weight	470 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...70 °C
Installation temperature	-40 °C...80 °C		

Cable specific standards

Standard, additional standards	UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8	Standard, assembly	UL-Style 21694
Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

Cable structure

Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Complete shielding	Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*AWG 22/7 - 0.32 mm ²
Diameter of inner sheathing	4.05 mm	Filler	As central element
Insulation	PE	Insulation cross-section	1.5 mm
Material sheath	PVC	Number of wires	4
Overlap of shielding braid	85 %	Sheath diameter, max.	6.7 mm
Sheath diameter, min.	6.3 mm	Sheathing colour	green (RAL 6018)
Sheathing material thickness	0.9 mm	Shielding	SF/UTP
Shielding braid thickness	0.13 mm	Standard designations	2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN
Strands	7	Wire material	Stranded tin-plated copper wire

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Characteristic impedance	100 ± 5 Ω at 100MHz
Loop resistance	120 Ω/km	Operating voltage (UL rating)	600 V
Operating voltage, UL	600 V	Signal propagation time	5.3 ns/m
Test voltage: wire-wire-shield	2000 V _{eff} , 50 Hz, 1 min	Transfer impedance	20 mΩ/m at 10 MHz

Mechanical and material properties of cable

Abrasion resistance	good	Halogen	Yes
Min. bending radius, once only	3.5 *diameter	Min. bending radius, repetitive	7.5 x cable diameter
Resistance to spread of flame	in accordance with IEC 60332-1 / UL 1685		

Plug

Plug left	RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded	Plug right	RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded
-----------	--	------------	--

Creation date June 16, 2025 5:36:36 PM CEST

IE-C5DS4VG0065A20A20-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Plug, left

Plug left	RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded
-----------	--

Plug, right

Plug right	RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded
------------	--

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/ https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/
ROHS	Conform

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN