

ESG 9/17 K MC NE BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ESG, Device markers x 17 mm, PA 66, Colour: blue, Self-adhesive
Order No.	1208960000
Type	ESG 9/17 K MC NE BL
GTIN (EAN)	403224899035 1
Qty.	200 pc(s).
compatible printer	2715590000 2438520000 2438510000

ESG 9/17 K MC NE BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	9 mm	Height (inches)	0.354 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	0.54 g		

Temperatures

Operating temperature range	-40...60 °C
-----------------------------	-------------

General data

Adhesive	Double-sided adhesive tape	
Application/manufacturer	Self-adhesive	
Colour	blue	
Halogen	No	
Material	PA 66	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Number per sheet	40	
Operating temperature range	-40...60 °C	
Operating temperature range, max.	60 °C	
Operating temperature range, min.	-40 °C	
Printed characters	without	
UL 94 flammability rating	V-2	
Version	Self-adhesive	
Width	17 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04
ECLASS 13.0	27-28-11-04	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Cradle to gate

0.003 kg CO2 eq.

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	de.myview.objectmodel.impl.BlockImpl@224f1916

ESG 9/17 K MC NE BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

[CAD data – DWG](#)

[CAD data – DXF](#)

Product Change Notification

[MultiCard Material modification](#)

[MultiCard Material Modifikation](#)

Catalogues

[Catalogues in PDF-format](#)

ESG 9/17 K MC NE BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

