

**WDK 2.5/D/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Why not integrating simple electrical functions into a feed through terminal. It has the same slim design of our feed-through terminal blocks - with additional functions such as cross-connections that can be used. Often, you only need a small component to integrate an external device into your automation technology. Our modular terminal blocks with electronic components make this possible; quickly, simply, and with a perfect fit.

**General ordering data**

|            |                                                                                                                                                  |
|------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Component terminal block, Screw connection, dark beige, 2.5 mm <sup>2</sup> , 400 V, 400 V, Number of connections: 4, Number of levels: 2, TS 35 |
| Order No.  | <a href="#">1023100000</a>                                                                                                                       |
| Type       | WDK 2.5/D/3                                                                                                                                      |
| GTIN (EAN) | 4008190173784                                                                                                                                    |
| Qty.       | 50 pc(s).                                                                                                                                        |

## WDK 2.5/D/3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                |            |
|--------------------------|------------|----------------|------------|
| Depth                    | 62.5 mm    | Depth (inches) | 2.461 inch |
| Depth including DIN rail | 63 mm      | Height         | 69 mm      |
| Height (inches)          | 2.717 inch | Width          | 5.1 mm     |
| Width (inches)           | 0.201 inch | Net weight     | 12.63 g    |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C        |

## Material data

|                           |       |        |            |
|---------------------------|-------|--------|------------|
| Material                  | Wemid | Colour | dark beige |
| UL 94 flammability rating | V-0   |        |            |

## System specifications

|                                     |                                                                                         |                               |     |
|-------------------------------------|-----------------------------------------------------------------------------------------|-------------------------------|-----|
| Version                             | Screw connection, with diode, for screwable cross-connection, One end without connector | End cover plate required      | Yes |
| Number of potentials                | 2                                                                                       | Number of levels              | 2   |
| Number of clamping points per level | 2                                                                                       | Number of potentials per tier | 1   |
| Levels cross-connected internally   | No                                                                                      | PE connection                 | No  |
| Rail                                | TS 35                                                                                   | N-function                    | No  |
| PE function                         | No                                                                                      | PEN function                  | No  |

## Additional technical data

|                          |       |                             |         |
|--------------------------|-------|-----------------------------|---------|
| Explosion-tested version | No    | Number of similar terminals | 1       |
| Open sides               | right | Type of mounting            | Snap-on |

## Conductors for clamping (rated connection)

|                                                                                         |                      |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|----------------------|-----------------------------------------------------------------------------------------|---------------------|
| Blade size                                                                              | 0.6 x 3.5 mm         | Clamping range, max.                                                                    | 4 mm <sup>2</sup>   |
| Clamping range, min.                                                                    | 0.05 mm <sup>2</sup> | Clamping screw                                                                          | M 2.5               |
| Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>    | Connection cross-section, stranded, min.                                                | 1.5 mm <sup>2</sup> |
| Connection direction                                                                    | on side              | Gauge to IEC 60947-1                                                                    | A3                  |
| Number of connections                                                                   | 4                    | Stripping length                                                                        | 10 mm               |
| Tightening torque, max.                                                                 | 0.6 Nm               | Tightening torque, min.                                                                 | 0.4 Nm              |
| Type of connection                                                                      | Screw connection     | Type of connection 2                                                                    | Screw connection    |
| Wire connection cross section AWG, max.                                                 | AWG 12               | Wire connection cross section AWG, min.                                                 | AWG 26              |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>    | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup>  | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>    | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup> |

## WDK 2.5/D/3

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Display element

Current 24 A

## General

|                                         |        |                                         |               |
|-----------------------------------------|--------|-----------------------------------------|---------------|
| Rail                                    | TS 35  | Standards                               | IEC 60947-7-1 |
| Wire connection cross section AWG, max. | AWG 12 | Wire connection cross section AWG, min. | AWG 26        |

## Rating data

|                                              |                     |                                 |               |
|----------------------------------------------|---------------------|---------------------------------|---------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 400 V         |
| Rated DC voltage                             | 400 V               | Rated current                   | 0.5 A         |
| Current at maximum wires                     | 24 A                | Standards                       | IEC 60947-7-1 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 6 kV          |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Pollution severity              | 3             |
| Surge voltage category                       | III                 |                                 |               |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000903    | ETIM 7.0    | EC000903    |
| ETIM 8.0    | EC000903    | ETIM 9.0    | EC000903    |
| ETIM 10.0   | EC000903    | ECLASS 9.0  | 27-14-11-27 |
| ECLASS 9.1  | 27-14-11-47 | ECLASS 10.0 | 27-14-11-27 |
| ECLASS 11.0 | 27-14-11-27 | ECLASS 12.0 | 27-14-11-27 |
| ECLASS 13.0 | 27-25-01-14 | ECLASS 14.0 | 27-25-01-14 |
| ECLASS 15.0 | 27-25-01-14 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Important note

|                     |                                                               |
|---------------------|---------------------------------------------------------------|
| Product information | The allowed continuous operating temperature must be observed |
|---------------------|---------------------------------------------------------------|

## Approvals

Approvals



|                 |                                                                                                                                                                                                                                                                                                                                                         |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/</a> |
| ROHS            | Conform                                                                                                                                                                                                                                                                                                                                                 |

## WDK 2.5/D/3

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|                                             |                                                                                                                                                                |
|---------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">CE Declaration of Conformity</a><br><a href="#">UKCA declaration of conformity</a><br><a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>                                                                                                                |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                       |

## Drawings

