

KLBUE 15-32 CPF16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection
Order No.	1252540000
Type	KLBUE 15-32 CPF16
GTIN (EAN)	4050118104424
Qty.	10 pc(s).

KLBUE 15-32 CPF16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	32 mm	Height (inches)	1.26 inch
Width	34.5 mm	Width (inches)	1.358 inch
Mounting dimension - width	33.5 mm	Net weight	91.4 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Material data

Colour	grey	UL 94 flammability rating	None
--------	------	---------------------------	------

System specifications

End cover plate required	No	Rail	TS 27
--------------------------	----	------	-------

Additional technical data

Explosion-tested version	No	Installation advice	C-rail with 16-mm opening
Type of mounting	Screw		

Conductors for clamping (rated connection)

Cable diameter, max.	32 mm	Cable diameter, min.	15 mm
Connection cross-section, stranded, max.	32 mm ²	Connection cross-section, stranded, min.	15 mm ²
Stripping length	32 mm	Type of connection	Spring connection

General

Installation advice	C-rail with 16-mm opening	Rail	TS 27
---------------------	---------------------------	------	-------

Rating data

Rated cross-section	32 mm ²
---------------------	--------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50
ECLASS 13.0	27-25-01-20	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		

Approvals

ROHS	Conform
------	---------

Cradle to gate

0.226 kg CO2 eq.

KLBUE 15-32 CPF16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	de.myview.objectmodel.impl.BlockImpl@4d56f5a9

Downloads

Engineering Data	CAD data – STEP CAD data – DWG CAD data – DXF
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	