


**SVF 7.62HP/02/180MSF2 SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

180° inverted inverse voltage-safe male header with PUSH IN connection technology for field wiring. With automatically locking middle flange for field wiring in 6 mm<sup>2</sup> with 7.62 pitch.

Also ideal as a touch-safe solution for inverse voltages. Meets the requirements of UL1059 600 V class C and IEC 61800-5-1.

On request, also available without middle flange.

**General ordering data**

|              |                                                                                                                                                                          |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male plug, 7.62 mm, Number of poles: 2, 180°, PUSH IN without actuator, Tension-clamp connection, Clamping range, max. : 10 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1061110000</a>                                                                                                                                               |
| Type         | SVF 7.62HP/02/180MSF2 SN BK BX                                                                                                                                           |
| GTIN (EAN)   | 4032248810659                                                                                                                                                            |
| Qty.         | 65 pc(s).                                                                                                                                                                |
| Product data | IEC: 1000 V / 57 A / 0.5 - 10 mm <sup>2</sup><br>UL: 600 V / 39 A / AWG 24 - AWG 10                                                                                      |
| Packaging    | Box                                                                                                                                                                      |

Creation date June 16, 2025 6:29:53 PM CEST

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 47.7 mm  | Depth (inches)  | 1.878 inch |
| Height     | 23.4 mm  | Height (inches) | 0.921 inch |
| Width      | 23.74 mm | Width (inches)  | 0.935 inch |
| Net weight | 12.6 g   |                 |            |

## System Parameters

|                                              |                                                    |                                            |                   |
|----------------------------------------------|----------------------------------------------------|--------------------------------------------|-------------------|
| Product family                               | OMNIMATE Power - series BV/SV 7.62HP               | Type of connection                         | Field connection  |
| Wire connection method                       | PUSH IN without actuator, Tension-clamp connection | Pitch in mm (P)                            | 7.62 mm           |
| Pitch in inches (P)                          | 0.3 "                                              | Conductor outlet direction                 | 180°              |
| Number of poles                              | 2                                                  | L1 in mm                                   | 15.24 mm          |
| L1 in inches                                 | 0.6 "                                              | Number of rows                             | 1                 |
| Pin series quantity                          | 1                                                  | Rated cross-section                        | 6 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch                             | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged      |
| Protection degree                            | IP20                                               | Volume resistance                          | 4.50 mΩ           |
| Can be coded                                 | Yes                                                | Stripping length                           | 12 mm             |
| Tightening torque for screw flange, min.     | 0.2 Nm                                             | Tightening torque for screw flange, max.   | 0.3 Nm            |
| Screwdriver blade                            | 0.6 x 3.5                                          | Plugging cycles                            | 25                |

## Material data

|                                       |                    |                                       |        |
|---------------------------------------|--------------------|---------------------------------------|--------|
| Insulating material                   | PA GF              | Colour                                | black  |
| Colour chart (similar)                | RAL 9011           | Insulating material group             | II     |
| Comparative Tracking Index (CTI)      | ≥ 500              | UL 94 flammability rating             | V-0    |
| Contact material                      | Cu-alloy           | Contact surface                       | tinned |
| Layer structure of plug contact       | 4...6 µm Sn glossy | Storage temperature, min.             | -40 °C |
| Storage temperature, max.             | 70 °C              | Operating temperature, min.           | -50 °C |
| Operating temperature, max.           | 125 °C             | Temperature range, installation, min. | -25 °C |
| Temperature range, installation, max. | 125 °C             |                                       |        |

## Conductors suitable for connection

|                                                                     |                     |
|---------------------------------------------------------------------|---------------------|
| Clamping range, min.                                                | 0.5 mm <sup>2</sup> |
| Clamping range, max.                                                | 10 mm <sup>2</sup>  |
| Solid, min. H05(07) V-U                                             | 0.5 mm <sup>2</sup> |
| Solid, max. H05(07) V-U                                             | 6 mm <sup>2</sup>   |
| Stranded, min. H07V-R                                               | 10 mm <sup>2</sup>  |
| Stranded, max. H07V-R                                               | 10 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                                          | 0.5 mm <sup>2</sup> |
| Flexible, max. H05(07) V-K                                          | 10 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 1.5 mm <sup>2</sup> min. |                     |
| w. plastic collar ferrule, DIN 46228 pt 4, 6 mm <sup>2</sup> max.   |                     |
| w. wire end ferrule, DIN 46228 pt 1, 1.5 mm <sup>2</sup> min.       |                     |
| w. wire end ferrule, DIN 46228 pt 1, 6 mm <sup>2</sup> max.         |                     |

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                     |                                                                                                                                                                        |                              |                             |       |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|-----------------------------|-------|
| Clampable conductor | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                  |       |
|                     |                                                                                                                                                                        | nominal                      | 2.5 mm <sup>2</sup>         |       |
|                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                     | 12 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H2.5/12</a>     |       |
|                     |                                                                                                                                                                        | Stripping length             | nominal                     | 14 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H2.5/19D BL</a> |       |
|                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                  |       |
|                     |                                                                                                                                                                        | nominal                      | 4 mm <sup>2</sup>           |       |
|                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                     | 12 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H4.0/12</a>     |       |
|                     |                                                                                                                                                                        | Stripping length             | nominal                     | 14 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H4.0/20D GR</a> |       |
|                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                  |       |
|                     |                                                                                                                                                                        | nominal                      | 6 mm <sup>2</sup>           |       |
|                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                     | 12 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H6.0/12</a>     |       |
|                     |                                                                                                                                                                        | Stripping length             | nominal                     | 14 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H6.0/20 SW</a>  |       |
|                     | Cross-section for conductor connection                                                                                                                                 | Type                         | fine-wired                  |       |
|                     |                                                                                                                                                                        | nominal                      | 1.5 mm <sup>2</sup>         |       |
|                     | wire end ferrule                                                                                                                                                       | Stripping length             | nominal                     | 15 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H1.5/18D SW</a> |       |
|                     |                                                                                                                                                                        | Stripping length             | nominal                     | 12 mm |
|                     |                                                                                                                                                                        | Recommended wire-end ferrule | <a href="#">H1.5/12</a>     |       |
| Reference text      | The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage. |                              |                             |       |

## Rated data acc. to IEC

|                                                                           |                        |  |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|--|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 |  | Rated current, min. number of poles (Tu=20°C)                         | 57 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 50 A                   |  | Rated current, min. number of poles (Tu=40°C)                         | 57 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 45 A                   |  | Rated voltage for surge voltage class / pollution degree II/2         | 1,000 V           |
| Rated voltage for surge voltage class / pollution degree III/2            | 800 V                  |  | Rated voltage for surge voltage class / pollution degree III/3        | 800 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6 kV                   |  | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 8 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 8 kV                   |  | Short-time withstand current resistance                               | 3 x 1s with 420 A |
| Clearance, min.                                                           | 12.7 mm                |  | Creepage distance, min.                                               | 12.7 mm           |

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

200039-1121690

|                                   |                                                                        |
|-----------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / CSA) | 600 V                                                                  |
| Rated voltage (Use group D / CSA) | 600 V                                                                  |
| Rated current (Use group C / CSA) | 36 A                                                                   |
| Wire cross-section, AWG, min.     | AWG 24                                                                 |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |

|                                   |        |
|-----------------------------------|--------|
| Rated voltage (Use group C / CSA) | 600 V  |
| Rated current (Use group B / CSA) | 36 A   |
| Rated current (Use group D / CSA) | 5 A    |
| Wire cross-section, AWG, max.     | AWG 10 |

## Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

|                                       |                                                                        |
|---------------------------------------|------------------------------------------------------------------------|
| Rated voltage (Use group B / UL 1059) | 600 V                                                                  |
| Rated voltage (Use group D / UL 1059) | 600 V                                                                  |
| Rated current (Use group C / UL 1059) | 39 A                                                                   |
| Wire cross-section, AWG, min.         | AWG 24                                                                 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |

|                                       |        |
|---------------------------------------|--------|
| Rated voltage (Use group C / UL 1059) | 600 V  |
| Rated current (Use group B / UL 1059) | 39 A   |
| Rated current (Use group D / UL 1059) | 5 A    |
| Wire cross-section, AWG, max.         | AWG 10 |

## Packing

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 352 mm |
| VPE width | 136 mm | VPE height | 60 mm  |

## Type tests

|                                              |            |                                                                                  |
|----------------------------------------------|------------|----------------------------------------------------------------------------------|
| Test: Durability of markings                 | Standard   | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96 |
|                                              | Test       | mark of origin, type identification, pitch                                       |
|                                              | Evaluation | available                                                                        |
|                                              | Test       | durability                                                                       |
| Test: Misengagement (Non-interchangeability) | Evaluation | passed                                                                           |
|                                              | Standard   | DIN EN 61984 section 6.3 and 6.9.1 / 09.02, DIN EN 60512-13-5 / 11.08            |
|                                              | Test       | 180° turned with coding elements                                                 |
|                                              | Evaluation | passed                                                                           |
|                                              | Test       | 180° turned without coding elements                                              |
|                                              | Evaluation | passed                                                                           |

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                                           |                |                                                                                    |
|-----------------------------------------------------------|----------------|------------------------------------------------------------------------------------|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 04.08 |
|                                                           | Conductor type | Type of conductor and solid 0.5 mm <sup>2</sup> conductor cross-section            |
|                                                           |                | Type of conductor and stranded 0.5 mm <sup>2</sup> conductor cross-section         |
|                                                           |                | Type of conductor and solid 6 mm <sup>2</sup> conductor cross-section              |
|                                                           |                | Type of conductor and stranded 6 mm <sup>2</sup> conductor cross-section           |
|                                                           |                | Type of conductor and AWG 24/1 conductor cross-section                             |
|                                                           |                | Type of conductor and AWG 24/19 conductor cross-section                            |
|                                                           |                | Type of conductor and AWG 14/1 conductor cross-section                             |
|                                                           |                | Type of conductor and AWG 14/19 conductor cross-section                            |
|                                                           | Evaluation     | passed                                                                             |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                                 |
|                                                           | Requirement    | 0.3 kg                                                                             |
|                                                           | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section                            |
|                                                           |                | Type of conductor and H05V-K0.5 conductor cross-section                            |
|                                                           |                | Type of conductor and AWG 20/1 conductor cross-section                             |
|                                                           |                | Type of conductor and AWG 20/19 conductor cross-section                            |
|                                                           | Evaluation     | passed                                                                             |
|                                                           | Requirement    | 1.4 kg                                                                             |
|                                                           | Conductor type | Type of conductor and H07V-U6 conductor cross-section                              |
|                                                           |                | Type of conductor and H07V-K6 conductor cross-section                              |
|                                                           |                | Type of conductor and AWG 10/1 conductor cross-section                             |
|                                                           |                | Type of conductor and AWG 10/19 conductor cross-section                            |
|                                                           | Evaluation     | passed                                                                             |

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|               |                |                                                         |
|---------------|----------------|---------------------------------------------------------|
| Pull-out test | Standard       | DIN EN 60999-1 section 9.5 / 12.00                      |
|               | Requirement    | ≥20 N                                                   |
|               | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section |
|               |                | Type of conductor and H05V-K0.5 conductor cross-section |
|               |                | Type of conductor and AWG 20/1 conductor cross-section  |
|               |                | Type of conductor and AWG 20/19 conductor cross-section |
|               | Evaluation     | passed                                                  |
|               | Requirement    | ≥80 N                                                   |
|               | Conductor type | Type of conductor and H07V-U6 conductor cross-section   |
|               |                | Type of conductor and H07V-K6 conductor cross-section   |
|               |                | Type of conductor and AWG 10/1 conductor cross-section  |
|               |                | Type of conductor and AWG 10/19 conductor cross-section |
|               | Evaluation     | passed                                                  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |
| ECLASS 13.0 | 27-46-02-02 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## SVF 7.62HP/02/180MSF2 SN BK BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                         |                                                                                                                                                                                                                                                                                                                                                         |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID         | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/</a> |
| ROHS                    | Conform                                                                                                                                                                                                                                                                                                                                                 |
| UL File Number Search   | UL Website                                                                                                                                                                                                                                                                                                                                              |
| Certificate No. (cURus) | E60693                                                                                                                                                                                                                                                                                                                                                  |

## Downloads

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                              |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                              |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                              |
| Product Change Notification                 | <a href="#">20220201 Visual change OMNIMATE® Power PCB terminal blocks and connectors</a><br><a href="#">20220201 Visuelle Änderung OMNIMATE® Power Leiterplattenklemmen und -steckverbinder</a>                                                                                                                                                                                                             |
| User Documentation                          | <a href="#">QR-Code product handling video</a>                                                                                                                                                                                                                                                                                                                                                               |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                     |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## SVF 7.62HP/02/180MSF2 SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings


## Product image



## Dimensional drawing



## Graph



## Graph

