

**THM GEW 30/8 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers.

Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Version            | THM, Device markers, 8 x 30 mm, yellow                |
| Order No.          | <a href="#">1114450000</a>                            |
| Type               | THM GEW 30/8 GE                                       |
| GTIN (EAN)         | 4032248892396                                         |
| Qty.               | 1 pc(s).                                              |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

## THM GEW 30/8 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 0.3 mm | Depth (inches)  | 0.012 inch |
| Height     | 8 mm   | Height (inches) | 0.315 inch |
| Width      | 30 mm  | Width (inches)  | 1.181 inch |
| Net weight | 957 g  |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -29...80 °C |
|-----------------------------|-------------|

## General data

|                                              |                               |            |
|----------------------------------------------|-------------------------------|------------|
| Adhesive                                     | Natural rubber adhesive       |            |
| Approval acc. to UL 969                      | No                            |            |
| Colour                                       | yellow                        |            |
| Halogen                                      | Yes                           |            |
| Material                                     | Cotton fabric                 |            |
| Material colour according to resistance code | 4                             |            |
| Number of markers per combination            | 1 Label reel = Device markers |            |
| Number of markers per packaging unit         | Form of supply                | Label reel |
| Number per roll                              | 10,000                        |            |
| Number per sheet                             | 10,000                        |            |
| Operating temperature range                  | -29...80 °C                   |            |
| Operating temperature range, max.            | 80 °C                         |            |
| Operating temperature range, min.            | -29 °C                        |            |
| Printed characters                           | without                       |            |
| Printing method                              | Thermal transfer              |            |
| UL 94 flammability rating                    | V-0                           |            |
| Version                                      | Self-adhesive                 |            |
| Width                                        | 30 mm                         |            |

## Device markers

|         |     |
|---------|-----|
| Halogen | Yes |
|---------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |
| ECLASS 13.0 | 27-28-11-04 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### THM GEW 30/8 GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues


[Catalogues in PDF-format](#)

**THM GEW 30/8 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**THM GEW 30/8 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

