


**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****Power on board - 100% safety, 100% integration, 100% cost-effectiveness:**

The compact, efficient solution for UL-600V applications in the lower performance range up to 12kVA.

- 29 A at 630 V (IEC)
- 20 A at 600 V (UL)
- Single compartment mating profile
- Clamping range: 0.08 - 4 mm<sup>2</sup> / AWG 28 - 12

Assistance with device approval:

- meets the requirements for 600 V in accordance with UL508/UL840
- meets the more stringent touch-safety requirements of IEC6100-5-1

The slimming cure for multiple-stage device series: reduced size and cut costs in the high-volume lower performance range without compromising device approval!

**General ordering data**

|              |                                                                                                                                                 |
|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, female plug, 7.62 mm, Number of poles: 7, 180°, Clamping yoke connection, Clamping range, max. : 4 mm <sup>2</sup> , Box |
| Order No.    | <a href="#">1164970000</a>                                                                                                                      |
| Type         | BLZ 7.62HP/07/180LR SN BK BX                                                                                                                    |
| GTIN (EAN)   | 4032248955053                                                                                                                                   |
| Qty.         | 20 pc(s).                                                                                                                                       |
| Product data | IEC: 630 V / 29 A / 0.2 - 4 mm <sup>2</sup><br>UL: 600 V / 20 A / AWG 20 - AWG 12                                                               |
| Packaging    | Box                                                                                                                                             |

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 23.3 mm  | Depth (inches)  | 0.917 inch |
| Height     | 18.3 mm  | Height (inches) | 0.72 inch  |
| Width      | 62.22 mm | Width (inches)  | 2.45 inch  |
| Net weight | 10.5 g   |                 |            |

**System Parameters**

|                                              |                                      |                                            |                     |
|----------------------------------------------|--------------------------------------|--------------------------------------------|---------------------|
| Product family                               | OMNIMATE Power - series BL/SL 7.62HP | Type of connection                         | Field connection    |
| Wire connection method                       | Clamping yoke connection             | Pitch in mm (P)                            | 7.62 mm             |
| Pitch in inches (P)                          | 0.3 "                                | Conductor outlet direction                 | 180°                |
| Number of poles                              | 7                                    | L1 in mm                                   | 45.72 mm            |
| L1 in inches                                 | 1.8 "                                | Number of rows                             | 1                   |
| Pin series quantity                          | 1                                    | Rated cross-section                        | 2.5 mm <sup>2</sup> |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch               | Touch-safe protection acc. to DIN VDE 0470 | IP 20               |
| Protection degree                            | IP20                                 | Volume resistance                          | 5.00 mΩ             |
| Can be coded                                 | Yes                                  | Stripping length                           | 7 mm                |
| Tightening torque, min.                      | 0.4 Nm                               | Tightening torque, max.                    | 0.5 Nm              |
| Clamping screw                               | M 2.5                                | Screwdriver blade                          | 0.6 x 3.5           |
| Screwdriver blade standard                   | DIN 5264                             | Plugging cycles                            | 25                  |
| Plugging force/pole, max.                    | 9.5 N                                | Pulling force/pole, max.                   | 8.5 N               |

**Material data**

|                                       |          |                                       |                            |
|---------------------------------------|----------|---------------------------------------|----------------------------|
| Insulating material                   | PBT      | Colour                                | black                      |
| Colour chart (similar)                | RAL 9011 | Insulating material group             | IIIa                       |
| Comparative Tracking Index (CTI)      | ≥ 200    | Insulation strength                   | ≥ 10 <sup>8</sup> Ω        |
| UL 94 flammability rating             | V-0      | Contact material                      | Cu-alloy                   |
| Contact surface                       | tinned   | Layer structure of plug contact       | 4...8 μm Sn hot-dip tinned |
| Storage temperature, min.             | -40 °C   | Storage temperature, max.             | 70 °C                      |
| Operating temperature, min.           | -50 °C   | Operating temperature, max.           | 100 °C                     |
| Temperature range, installation, min. | -25 °C   | Temperature range, installation, max. | 100 °C                     |

**Conductors suitable for connection**

|                                                                     |                      |
|---------------------------------------------------------------------|----------------------|
| Clamping range, min.                                                | 0.08 mm <sup>2</sup> |
| Clamping range, max.                                                | 4 mm <sup>2</sup>    |
| Wire connection cross section AWG, min.                             | AWG 28               |
| Wire connection cross section AWG, max.                             | AWG 12               |
| Solid, min. H05(07) V-U                                             | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                                             | 4 mm <sup>2</sup>    |
| Flexible, min. H05(07) V-K                                          | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                                          | 4 mm <sup>2</sup>    |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                      |
| w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |                      |
| w. wire end ferrule, DIN 46228 pt 1, min.                           | 0.2 mm <sup>2</sup>  |
| w. wire end ferrule, DIN 46228 pt 1, max.                           | 2.5 mm <sup>2</sup>  |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.8 mm x 2.4 mm      |

Creation date June 12, 2025 12:47:07 PM CEST

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|                     |                                        |                              |                              |
|---------------------|----------------------------------------|------------------------------|------------------------------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 0.25 mm <sup>2</sup>         |
|                     | wire end ferrule                       | Stripping length             | nominal 10 mm                |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.25/12 HBL</a> |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 0.34 mm <sup>2</sup>         |
|                     | wire end ferrule                       | Stripping length             | nominal 10 mm                |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.34/12 TK</a>  |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 0.5 mm <sup>2</sup>          |
|                     | wire end ferrule                       | Stripping length             | nominal 6 mm                 |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.5/6</a>       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 0.75 mm <sup>2</sup>         |
|                     | wire end ferrule                       | Stripping length             | nominal 6 mm                 |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.75/6</a>      |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 1 mm <sup>2</sup>            |
|                     | wire end ferrule                       | Stripping length             | nominal 6 mm                 |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.0/6</a>       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 1.5 mm <sup>2</sup>          |
|                     | wire end ferrule                       | Stripping length             | nominal 7 mm                 |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H1.5/7</a>       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                   |
|                     |                                        | nominal                      | 2.5 mm <sup>2</sup>          |
|                     | wire end ferrule                       | Stripping length             | nominal 7 mm                 |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H2.5/7</a>       |

Reference text The outside diameter of the plastic collar should not be larger than the pitch (P), Length of ferrules is to be chosen depending on the product and the rated voltage.

**Rated data acc. to IEC**

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 29 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 26.5 A                 | Rated current, min. number of poles (Tu=40°C)                         | 25 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 23 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 630 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 500 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 400 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 4 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 6 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 6 kV                   | Short-time withstand current resistance                               | 3 x 1s with 180 A |
| Clearance, min.                                                           | 9.8 mm                 | Creepage distance, min.                                               | 11.3 mm           |

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Rated data acc. to CSA**

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 600 V  | Rated voltage (Use group C / CSA) | 600 V  |
| Rated voltage (Use group D / CSA) | 600 V  | Rated current (Use group B / CSA) | 20 A   |
| Rated current (Use group C / CSA) | 20 A   | Rated current (Use group D / CSA) | 5 A    |
| Wire cross-section, AWG, min.     | AWG 20 | Wire cross-section, AWG, max.     | AWG 12 |

**Rated data acc. to UL 1059**

Institute (cURus)



Certificate No. (cURus)

E60693

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 600 V                                                                  | Rated voltage (Use group C / UL 1059) | 600 V  |
| Rated voltage (Use group D / UL 1059) | 600 V                                                                  | Rated current (Use group B / UL 1059) | 20 A   |
| Rated current (Use group C / UL 1059) | 20 A                                                                   | Rated current (Use group D / UL 1059) | 5 A    |
| Wire cross-section, AWG, min.         | AWG 20                                                                 | Wire cross-section, AWG, max.         | AWG 12 |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

**Packing**

|           |        |            |        |
|-----------|--------|------------|--------|
| Packaging | Box    | VPE length | 345 mm |
| VPE width | 135 mm | VPE height | 34 mm  |

**Type tests**

|                                              |            |                                                                                  |
|----------------------------------------------|------------|----------------------------------------------------------------------------------|
| Test: Durability of markings                 | Standard   | DIN EN 61984 section 7.3.2 / 09.02 taking pattern from DIN EN 60068-2-70 / 07.96 |
|                                              | Test       | mark of origin, type identification, pitch, type of material, date clock         |
|                                              | Evaluation | available                                                                        |
|                                              | Test       | durability                                                                       |
| Test: Misengagement (Non-interchangeability) | Evaluation | passed                                                                           |
|                                              | Standard   | DIN EN 61984 section 6.3 and 6.9.1 / 09.02                                       |
|                                              | Test       | 180° turned with coding elements                                                 |
|                                              | Evaluation | passed                                                                           |
|                                              | Test       | 180° turned without coding elements                                              |
|                                              | Evaluation | passed                                                                           |

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|                                                           |                |                                                                                    |  |
|-----------------------------------------------------------|----------------|------------------------------------------------------------------------------------|--|
| Test: Clampable cross section                             | Standard       | DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02 |  |
|                                                           | Conductor type | Type of conductor and solid 0.5 mm <sup>2</sup> conductor cross-section            |  |
|                                                           |                | Type of conductor and stranded 0.5 mm <sup>2</sup> conductor cross-section         |  |
|                                                           |                | Type of conductor and solid 2.5 mm <sup>2</sup> conductor cross-section            |  |
|                                                           |                | Type of conductor and stranded 2.5 mm <sup>2</sup> conductor cross-section         |  |
|                                                           |                | Type of conductor and AWG 20/1 conductor cross-section                             |  |
|                                                           |                | Type of conductor and AWG 20/19 conductor cross-section                            |  |
|                                                           |                | Type of conductor and AWG 12/1 conductor cross-section                             |  |
|                                                           |                | Type of conductor and AWG 12/19 conductor cross-section                            |  |
|                                                           | Evaluation     | passed                                                                             |  |
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                                 |  |
|                                                           | Requirement    | 0.2 kg                                                                             |  |
|                                                           | Conductor type | Type of conductor and AWG 28/1 conductor cross-section                             |  |
|                                                           |                | Type of conductor and AWG 28/19 conductor cross-section                            |  |
|                                                           | Evaluation     | passed                                                                             |  |
|                                                           | Requirement    | 0.3 kg                                                                             |  |
|                                                           | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section                            |  |
|                                                           |                | Type of conductor and H05V-K0.5 conductor cross-section                            |  |
|                                                           | Evaluation     | passed                                                                             |  |
|                                                           | Requirement    | 0.7 kg                                                                             |  |
|                                                           | Conductor type | Type of conductor and AWG 14/1 conductor cross-section                             |  |
|                                                           |                | Type of conductor and AWG 14/19 conductor cross-section                            |  |
|                                                           | Evaluation     | passed                                                                             |  |
|                                                           | Requirement    | 0.9 kg                                                                             |  |
|                                                           | Conductor type | Type of conductor and H07V-U4.0 conductor cross-section                            |  |
|                                                           |                | Type of conductor and H07V-K4.0 conductor cross-section                            |  |
|                                                           | Evaluation     | passed                                                                             |  |

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data**

|               |                |                                                         |
|---------------|----------------|---------------------------------------------------------|
| Pull-out test | Standard       | DIN EN 60999-1 section 9.5 / 12.00                      |
|               | Requirement    | ≥5 N                                                    |
|               | Conductor type | Type of conductor and AWG 28/1 conductor cross-section  |
|               |                | Type of conductor and AWG 28/19 conductor cross-section |
|               | Evaluation     | passed                                                  |
|               | Requirement    | ≥20 N                                                   |
|               | Conductor type | Type of conductor and H05V-U0.5 conductor cross-section |
|               |                | Type of conductor and H05V-K0.5 conductor cross-section |
|               | Evaluation     | passed                                                  |
|               | Requirement    | ≥50 N                                                   |
|               | Conductor type | Type of conductor and AWG 14/1 conductor cross-section  |
|               |                | Type of conductor and AWG 14/19 conductor cross-section |
|               |                | Type of conductor and H07V-K4.0 conductor cross-section |
|               | Evaluation     | passed                                                  |
|               | Requirement    | ≥60 N                                                   |
|               | Conductor type | Type of conductor and H07V-U4.0 conductor cross-section |
|               | Evaluation     | passed                                                  |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002638    | ETIM 7.0    | EC002638    |
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 9.0  | 27-44-03-09 |
| ECLASS 9.1  | 27-44-03-09 | ECLASS 10.0 | 27-44-03-09 |
| ECLASS 11.0 | 27-46-02-02 | ECLASS 12.0 | 27-46-02-02 |
| ECLASS 13.0 | 27-46-02-02 | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |

Cradle to gate

0.291 kg CO<sub>2</sub>eq.**Environmental Product Compliance**

|                          |                                              |
|--------------------------|----------------------------------------------|
| RoHS Compliance Status   | Compliant without exemption                  |
| REACH SVHC               | No SVHC above 0.1 wt%                        |
| Product Carbon Footprint | de.myview.objectmodel.impl.BlockImpl@e7ea326 |

**BLZ 7.62HP/07/180LR SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Important note**

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Gold-plated contact surfaces on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

**Approvals**

Approvals



|                         |                                                                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID         | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/</a> |
| ROHS                    | Conform                                                                                                                                                                     |
| UL File Number Search   | UL Website                                                                                                                                                                  |
| Certificate No. (cURus) | E60693                                                                                                                                                                      |

**Downloads**

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                              |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                              |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                              |
| Product Change Notification                 | <a href="#">20220208 Visual change Temporarily different color for connectors and accessories</a><br><a href="#">20220208 Visuelle Änderung Vorübergehend anderer Farbton für Steckverbinder und Zubehör</a><br><a href="#">20220627 Change OMNIMATE® Power BLZ 7.62HP</a><br><a href="#">20220627 Technische Änderung OMNIMATE® Power BLZ 7.62HP</a>                                                        |
| User Documentation                          | <a href="#">QR-Code product handling video</a>                                                                                                                                                                                                                                                                                                                                                               |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                     |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |

Creation date June 12, 2025 12:47:07 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.


## BLZ 7.62HP/07/180LR SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings


## Product image




## Dimensional drawing



## Graph



## Graph









The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmueller Interface GmbH & Co. KG

The English version is binding



|    |         |           |
|----|---------|-----------|
| 12 | 83,82   | 3,300     |
| 11 | 76,20   | 3,000     |
| 10 | 68,58   | 2,700     |
| 9  | 60,96   | 2,400     |
| 8  | 53,34   | 2,100     |
| 7  | 45,72   | 1,800     |
| 6  | 38,10   | 1,500     |
| 5  | 30,48   | 1,200     |
| 4  | 22,86   | 0,900     |
| 3  | 15,24   | 0,600     |
| 2  | 7,62    | 0,300     |
| n  | L1 [mm] | L1 [Inch] |

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance to VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmueller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

P=Raster/pitch  
shown: BLZ 7.62HP/05/180LR



|                                                                                                                                              |                 |                                                                                       |                                                                                                               |  |
|----------------------------------------------------------------------------------------------------------------------------------------------|-----------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|--|
| General Tolerances: <input type="checkbox"/> WN700144-W.. <input type="checkbox"/> WN 212010 <input checked="" type="checkbox"/> ISO 2768-mK |                 |                                                                                       | Tolerances ISO 8015                                                                                           |  |
| Changes: EC00007383                                                                                                                          |                 |                                                                                       | <div>49781</div> <div>Drawing no. <span></span> Index <span>10</span></div> <div>Scale: 2:1 Sheet 2 / 3</div> |  |
| Mat. No. (SAP) 1095700000                                                                                                                    |                 |                                                                                       |                                                                                                               |  |
| Drawings Assembly                                                                                                                            |                 |                                                                                       |                                                                                                               |  |
| Drawn                                                                                                                                        | Helis, Maria    |  | <div>BLZ 7.62HP/./180LH/LR</div> <div>SOCKET BLOCK</div> <div>BUCHSENLEISTE</div>                             |  |
| Responsible                                                                                                                                  | Hertel, Suzanne |                                                                                       |                                                                                                               |  |
| Approved                                                                                                                                     | Lang, Thomas    |                                                                                       |                                                                                                               |  |
| 13.10.2022                                                                                                                                   |                 |                                                                                       |                                                                                                               |  |

10

Index