

**HSS-HF 4.8-9.5 EL Y75M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |                                                             |
|--------------------|-------------------------------------------------------------|
| Version            | TwinMark, Conductor and cable markers, 4.8 - 9.5 mm, yellow |
| Order No.          | <a href="#">1562690000</a>                                  |
| Type               | HSS-HF 4.8-9.5 EL Y75M                                      |
| GTIN (EAN)         | 4050118367522                                               |
| Qty.               | 1 pc(s).                                                    |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>       |

## HSS-HF 4.8-9.5 EL Y75M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |           |                 |               |
|------------|-----------|-----------------|---------------|
| Depth      | 0.77 mm   | Depth (inches)  | 0.03 inch     |
| Width      | 15.1 mm   | Width (inches)  | 0.594 inch    |
| Length     | 75,000 mm | Length (inches) | 2,952.75 inch |
| Net weight | 1,377 g   |                 |               |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

## General data

|                                      |                                                    |                    |
|--------------------------------------|----------------------------------------------------|--------------------|
| Colour                               | yellow                                             |                    |
| Halogen                              | No                                                 |                    |
| Length                               | 75,000 mm                                          |                    |
| Material                             | Polyolefine                                        |                    |
| Number of markers per combination    | 1 Shrink sleeve reel = Conductor and cable markers |                    |
| Number of markers per packaging unit | Form of supply                                     | Shrink sleeve reel |
| Number per roll                      | 1                                                  |                    |
| Operating temperature range          | -55... 105 °C                                      |                    |
| Operating temperature range, max.    | 105 °C                                             |                    |
| Operating temperature range, min.    | -55 °C                                             |                    |
| Printed characters                   | without                                            |                    |
| Type of printing                     | neutral                                            |                    |
| Width                                | 15.1 mm                                            |                    |

## Conductor and cable markers

|                                   |                   |                                  |                        |
|-----------------------------------|-------------------|----------------------------------|------------------------|
| Conductor O.D.                    | 4.8 - 9.5 mm      | Conductor O.D., max.             | 9.5 mm                 |
| Conductor O.D., min.              | 4.8 mm            | Conductor cross-section, max.    | 16 mm <sup>2</sup>     |
| Conductor cross-section, min.     | 4 mm <sup>2</sup> | Cross-section for connected wire | 4 - 16 mm <sup>2</sup> |
| Halogen                           | No                | Rate of shrinkage                | 2:1                    |
| Recommended shrinking temperature | 90 °C             |                                  |                        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |
| ECLASS 13.0 | 27-28-11-02 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Important note

|                     |                                           |
|---------------------|-------------------------------------------|
| Product information | External roll holder 1302920000 necessary |
|---------------------|-------------------------------------------|

## HSS-HF 4.8-9.5 EL Y75M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                                             |                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">NFX 70-100-1 2006 + NF X 70-100-2 2006</a><br><a href="#">BS EN ISO 4589-2 1999</a><br><a href="#">EN 45545-2:2020</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                           |