

**LM MT300 25.4/12.7 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

|            |                                                  |
|------------|--------------------------------------------------|
| Version    | LaserMark, Device markers, 12.7 x 25.4 mm, white |
| Order No.  | <a href="#">1686391044</a>                       |
| Type       | LM MT300 25.4/12.7 WS                            |
| GTIN (EAN) | 4008190493974                                    |
| Qty.       | 10 pc(s).                                        |

## LM MT300 25.4/12.7 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.003 inch |
| Height     | 12.7 mm | Height (inches) | 0.5 inch   |
| Width      | 25.4 mm | Width (inches)  | 1 inch     |
| Net weight | 11.8 g  |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                              |                                           |             |  |
|----------------------------------------------|-------------------------------------------|-------------|--|
| Adhesive                                     | Acrylate adhesive                         |             |  |
| Approval acc. to UL 969                      | Yes                                       |             |  |
| Colour                                       | white                                     |             |  |
| Halogen                                      | No                                        |             |  |
| Material                                     | Polyester, PVC-free                       |             |  |
| Material colour according to resistance code | 9                                         |             |  |
| Number of markers per combination            | 1 Label sheet = 147 Device markers        |             |  |
| Number of markers per packaging unit         | 1,470                                     |             |  |
| Number of markers per packaging unit         | Number of markers per combination         | 147         |  |
|                                              | Number of combinations per packaging unit | 10          |  |
|                                              | Form of supply                            | Label sheet |  |
| Number per sheet                             | 147                                       |             |  |
| Operating temperature range                  | -40... 150 °C                             |             |  |
| Operating temperature range, max.            | 150 °C                                    |             |  |
| Operating temperature range, min.            | -40 °C                                    |             |  |
| Printed characters                           | without                                   |             |  |
| Printing method                              | Laser print                               |             |  |
| UL 94 flammability rating                    | HB                                        |             |  |
| Version                                      | Self-adhesive                             |             |  |
| Width                                        | 25.4 mm                                   |             |  |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |
| ECLASS 13.0 | 27-28-11-04 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## LM MT300 25.4/12.7 WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS

Conform

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**LM MT300 25.4/12.7 WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

