

LM WO 18/34 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 5 - 7 mm, 18 x 34 mm, white
Order No.	1695711044
Type	LM WO 18/34 WS
GTIN (EAN)	4008190924652
Qty.	10 pc(s).

LM WO 18/34 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	18 mm	Height (inches)	0.709 inch
Width	34 mm	Width (inches)	1.339 inch
Net weight	10.2 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate		
Colour	white		
Halogen	No		
Material	Polyester film		
Material colour according to resistance code	9		
Number of markers per combination	1 Label sheet = 88 Conductor and cable markers		
Number of markers per packaging unit	880		
Number of markers per packaging unit	Number of markers per combination	88	
	Number of combinations per packaging unit	10	
	Form of supply	Label sheet	
Number per sheet	88		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printed characters	without		
Size of labelling field	17.8 x 13 mm		
Type of printing	neutral		
UL 94 flammability rating	V-0		
Version	Self-adhesive		
Width	34 mm		

Conductor and cable markers

Conductor O.D.	5 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	5 mm	Conductor cross-section, max.	16 mm ²
Conductor cross-section, min.	6 mm ²	Cross-section for connected wire	6 - 16 mm ²
Halogen	No	Text field height	17.8 mm
Text field width	13 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

LM WO 18/34 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

