

TM-I 15 MC NE VI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility. The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	TM-I, Insert markers, 15 x 4 mm, violet
Order No.	1427870000
Type	TM-I 15 MC NE VI
GTIN (EAN)	4050118231847
Qty.	400 pc(s).
Alternative product	1609990000
compatible printer	2715590000 2438520000 2438510000

TM-I 15 MC NE VI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	15 mm	Height (inches)	0.591 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.265 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Colour	violet	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Insert markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Orientation of print	horizontal and vertical	
Printed characters	without	
Recommended industries	Transportation, Machinery	
Type of printing	neutral	
UL 94 flammability rating	V-2	
Width	4 mm	

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

TM-I 15 MC NE VI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

