

HDC CM 10 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HD-series crimp contacts are used with the CM10 module. The crimp contact features a stainless steel spring. The top spring provides a secure and permanent grip on the crimp contact in the module.

Customized contact-release tools are available for taking apart the contacts. The CM10 module can be ordered with or without the integrated module-release aid. A removal tool is available for those modules that do not feature an integrated module-release aid.

General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept module
Order No.	1758400000
Type	HDC CM 10 MC
GTIN (EAN)	4032248019625
Qty.	10 pc(s).

HDC CM 10 MC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Height	29.4 mm	Height (inches)	1.157 inch
Width	11.4 mm	Width (inches)	0.449 inch
Net weight	6.97 g		

ConCept Pneumatic module

Colour	beige	UL 94 flammability rating	V-0
--------	-------	---------------------------	-----

Dimensions

Height of plug	29.4 mm	Total length base	34 mm
Width	11.4 mm		

General data

Colour	beige	Free from halogens	false
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Insulation strength	10 ¹¹ Ω
Low smoke acc. DIN EN 45545-2		Material	Polycarbonate, glass fibre reinforced
Number of poles	10	Pollution severity	3
Rated current (DIN EN 61984)	10 A	Rated impulse voltage (DIN EN 61984)	4 kV
Rated voltage (DIN EN 61984)	250 V	Series	ConCept module
Surge voltage category	III	Type	Pin
Type of connection	Crimp connection	UL 94 flammability rating	V-0
Volume resistance	≤4 mΩ		

Connection data PE

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

Version

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.14 mm ²
Material	Polycarbonate, glass fibre reinforced	Stripping length, rated connection	8 mm
Type of connection	Crimp connection	Volume resistance	≤4 mΩ
Wire connection cross section AWG, max.	AWG 14	Wire connection cross section AWG, min.	AWG 26

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC000438
ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 9.0	27-44-02-05
ECLASS 9.1	27-44-02-05	ECLASS 10.0	27-44-02-05
ECLASS 11.0	27-44-02-05	ECLASS 12.0	27-44-02-05
ECLASS 13.0	27-44-02-05	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		

HDC CM 10 MC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

HDC CM 10 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

