

**WSMH 84MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

WSM is a complete marking system for cables, conductors, pipes and components - it offers permanent labelling in environments which no other marker is able to withstand. This product line consists of labelling plates, carriers and stainless steel cable ties – available individually or complete in the WSM Set and Service Box.

**Advantages:**

- Sturdy embossed characters for maximum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire, etc.
- Individual and multi-character markings, can also be combined
- Quick installation
- Ideal for outdoor applications
- Easy attachment with cable ties

**General ordering data**

Version	Stainless steel markers, Conductor and cable markers, 14 - 79 mm, 84 x 11 mm, silver
Order No.	<a href="#">1774520000</a>
Type	WSMH 84MM
GTIN (EAN)	4032248149315
Qty.	50 pc(s).

## WSMH 84MM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	84 mm	Height (inches)	3.307 inch
Width	11 mm	Width (inches)	0.433 inch
Net weight	2.73 g		

## Temperatures

Operating temperature range	250 °C
-----------------------------	--------

## General data

Colour	silver
Material	Stainless steel 1.4404
Number of characters	12
Number of markers per combination	1 Component part = Conductor and cable markers
Number of markers per packaging unit	Form of supply
	Component part
Number per roll	50
Operating temperature range	250 °C
Operating temperature range, max.	250 °C
Printed characters	without
Type of printing	neutral
Width	11 mm

## Conductor and cable markers

Conductor O.D.	14 - 79 mm	Conductor O.D., max.	79 mm
Conductor O.D., min.	14 mm	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 500 mm <sup>2</sup>

## Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02
ECLASS 13.0	27-28-11-02	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Approvals

ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--