


**LSF-SMT 3.81/15/180 3.5SN BK TU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

PCB terminal for fully automatic assembly in reflow soldering (SMT), with PUSH IN conductor connection system. Conductor inserted and slider operated in same direction (TOP). Packed in box or as tape on reel. Pin lengths optimised at 1.5 mm or 3.5 mm.

**General ordering data**

|              |                                                                                                                                                                       |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | Printed circuit board terminals, 3.81 mm, Number of poles: 15, 180°, Solder pin length (l): 3.5 mm, black, PUSH IN with actuator, Clamping range, max.: 1.5 mm², Tube |
| Order No.    | <a href="#">1870920000</a>                                                                                                                                            |
| Type         | LSF-SMT 3.81/15/180 3.5SN BK TU                                                                                                                                       |
| GTIN (EAN)   | 4032248448319                                                                                                                                                         |
| Qty.         | 9 pc(s).                                                                                                                                                              |
| Product data | IEC: 320 V / 17.5 A / 0.2 - 1.5 mm²<br>UL: 300 V / 12 A / AWG 28 - AWG 14                                                                                             |
| Packaging    | Tube                                                                                                                                                                  |

Creation date June 12, 2025 12:51:10 PM CEST

## LSF-SMT 3.81/15/180 3.5SN BK TU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Depth                    | 7.8 mm     | Depth (inches)  | 0.307 inch |
| Height                   | 17.5 mm    | Height (inches) | 0.689 inch |
| Height of lowest version | 14 mm      | Width           | 57.54 mm   |
| Width (inches)           | 2.265 inch | Net weight      | 12.22 g    |

## Temperatures

|                                  |        |
|----------------------------------|--------|
| Continuous operating temp., max. | 120 °C |
|----------------------------------|--------|

## System parameters

|                                            |                              |                                              |                        |
|--------------------------------------------|------------------------------|----------------------------------------------|------------------------|
| Product family                             | OMNIMATE Signal - series LSF | Wire connection method                       | PUSH IN with actuator  |
| Mounting onto the PCB                      | THT/THR solder connection    | Conductor outlet direction                   | 180°                   |
| Pitch in mm (P)                            | 3.81 mm                      | Pitch in inches (P)                          | 0.15 "                 |
| Number of poles                            | 15                           | Pin series quantity                          | 1                      |
| Fitted by customer                         | No                           | Number of rows                               | 1                      |
| Solder pin length (l)                      | 3.5 mm                       | Solder pin length tolerance                  | +0.1 / -0.3 mm         |
| Solder pin dimensions                      | 0.35 x 0.8 mm                | Solder pin dimensions = d tolerance          | 0 / -0.1 mm            |
| Solder eyelet hole diameter (D)            | 1.1 mm                       | Solder eyelet hole diameter tolerance (D)    | + 0,1 mm               |
| Number of solder pins per pole             | 2                            | Stripping length                             | 8 mm                   |
| L1 in mm                                   | 53.34 mm                     | L1 in inches                                 | 2.1 "                  |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                        | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch |
| Protection degree                          | IP20                         | Volume resistance                            | 1.60 mΩ                |

## Material data

|                                       |                  |                                       |          |
|---------------------------------------|------------------|---------------------------------------|----------|
| Insulating material                   | LCP GF           | Colour                                | black    |
| Colour chart (similar)                | RAL 9011         | Insulating material group             | IIIa     |
| Comparative Tracking Index (CTI)      | ≥ 175            | Moisture Level (MSL)                  | 1        |
| UL 94 flammability rating             | V-0              | Contact material                      | Cu-alloy |
| Layer structure of solder connection  | 4...6 µm Sn matt | Storage temperature, min.             | -40 °C   |
| Storage temperature, max.             | 70 °C            | Operating temperature, min.           | -50 °C   |
| Operating temperature, max.           | 120 °C           | Temperature range, installation, min. | -30 °C   |
| Temperature range, installation, max. | 120 °C           |                                       |          |

## Conductors suitable for connection

|                                                                      |                      |
|----------------------------------------------------------------------|----------------------|
| Clamping range, min.                                                 | 0.13 mm <sup>2</sup> |
| Clamping range, max.                                                 | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.                              | AWG 28               |
| Wire connection cross section AWG, max.                              | AWG 14               |
| Solid, min. H05(07) V-U                                              | 0.2 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U                                              | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                                           | 0.2 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K                                           | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.25 mm <sup>2</sup> min. |                      |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.75 mm <sup>2</sup> max. |                      |
| w. wire end ferrule, DIN 46228 pt 1, 0.25 mm <sup>2</sup> min.       |                      |

Creation date June 12, 2025 12:51:10 PM CEST

## LSF-SMT 3.81/15/180 3.5SN BK TU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

w. wire end ferrule, DIN 46228 pt 1, max. 1.5 mm<sup>2</sup>

|                     |                                        |                              |                               |       |
|---------------------|----------------------------------------|------------------------------|-------------------------------|-------|
| Clampable conductor | Cross-section for conductor connection | Type                         | fine-wired                    |       |
|                     |                                        | nominal                      | 0.25 mm <sup>2</sup>          |       |
|                     | wire end ferrule                       | Stripping length             | nominal                       | 10 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.25/12 HBL</a>  |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                    |       |
|                     |                                        | nominal                      | 0.34 mm <sup>2</sup>          |       |
|                     | wire end ferrule                       | Stripping length             | nominal                       | 10 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.34/12 TK</a>   |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                    |       |
|                     |                                        | nominal                      | 0.5 mm <sup>2</sup>           |       |
|                     | wire end ferrule                       | Stripping length             | nominal                       | 10 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.5/14 OR</a>    |       |
|                     | Cross-section for conductor connection | Type                         | fine-wired                    |       |
|                     |                                        | nominal                      | 0.75 mm <sup>2</sup>          |       |
|                     | wire end ferrule                       | Stripping length             | nominal                       | 10 mm |
|                     |                                        | Recommended wire-end ferrule | <a href="#">H0.75/14T HBL</a> |       |

Reference text Length of ferrules is to be chosen depending on the product and the rated voltage.. The outside diameter of the plastic collar should not be larger than the pitch (P)

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                  |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=20°C)                             | 16 A                   | Rated current, min. number of poles (Tu=40°C)                         | 17.5 A           |
| Rated current, max. number of poles (Tu=40°C)                             | 14 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 320 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 160 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 160 V            |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 2.5 kV                 | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV           |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 2.5 kV                 | Short-time withstand current resistance                               | 3 x 1s with 80 A |

## Rated data acc. to CSA

|                                   |                                                                                     |                                   |                |
|-----------------------------------|-------------------------------------------------------------------------------------|-----------------------------------|----------------|
| Institute (CSA)                   |  | Certificate No. (CSA)             | 200039-1664286 |
| Rated voltage (Use group B / CSA) | 300 V                                                                               | Rated voltage (Use group D / CSA) | 300 V          |
| Rated current (Use group B / CSA) | 10 A                                                                                | Rated current (Use group D / CSA) | 10 A           |
| Wire cross-section, AWG, min.     | AWG 28                                                                              | Wire cross-section, AWG, max.     | AWG 14         |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate.              |                                   |                |

## LSF-SMT 3.81/15/180 3.5SN BK TU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to UL 1059

Institute (cURus)



Certificate No. (cURus)

E60693

Rated voltage (Use group B / UL 1059) 300 V

Rated current (Use group B / UL 1059) 12 A

Wire cross-section, AWG, min. AWG 28

Reference to approval values Specifications are maximum values, details - see approval certificate.

Rated voltage (Use group D / UL 1059) 300 V

Rated current (Use group D / UL 1059) 10 A

Wire cross-section, AWG, max. AWG 14

## Packing

Packaging Tube

VPE width 21 mm

Surface resistance  $R_s = 10^9 - 10^{12} \Omega$ 

VPE length 556 mm

VPE height 16 mm

## Type tests

Test: Durability of markings

Standard

DIN EN 60512-1-1 / 01.03

Test

mark of origin, type identification, pitch, durability

Evaluation

available

Test

approval marking UL

Evaluation

on packaging label

Test: Clampable cross section

Standard

DIN EN 60999-1 section 7 and 9.1 / 12.00, DIN EN 60947-1 section 8.2.4.5.1 / 12.02

Conductor type

Type of conductor and solid 0.14 mm<sup>2</sup> conductor cross-sectionType of conductor and stranded 0.14 mm<sup>2</sup> conductor cross-sectionType of conductor and solid 1.5 mm<sup>2</sup> conductor cross-sectionType of conductor and stranded 1.5 mm<sup>2</sup> conductor cross-section

Type of conductor and AWG 24/1 conductor cross-section

Type of conductor and AWG 24/19 conductor cross-section

Type of conductor and AWG 16/1 conductor cross-section

Type of conductor and AWG 16/19 conductor cross-section

Evaluation

passed

## LSF-SMT 3.81/15/180 3.5SN BK TU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                                                           |                |                                                                             |
|-----------------------------------------------------------|----------------|-----------------------------------------------------------------------------|
| Test for damage to and accidental loosening of conductors | Standard       | DIN EN 60999-1 section 9.4 / 12.00                                          |
|                                                           | Requirement    | 0.2 kg                                                                      |
|                                                           | Conductor type | Type of conductor and AWG 24/1 conductor cross-section                      |
|                                                           |                | Type of conductor and AWG 24/19 conductor cross-section                     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Requirement    | 0.3 kg                                                                      |
|                                                           | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section |
|                                                           |                | Type of conductor and solid 0.5 mm <sup>2</sup> conductor cross-section     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Requirement    | 0.4 kg                                                                      |
| Pull-out test                                             | Conductor type | Type of conductor and solid 1.5 mm <sup>2</sup> conductor cross-section     |
|                                                           |                | Type of conductor and stranded 1.5 mm <sup>2</sup> conductor cross-section  |
|                                                           | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|                                                           |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Standard       | DIN EN 60999-1 section 9.5 / 12.00                                          |
|                                                           | Requirement    | ≥10 N                                                                       |
|                                                           | Conductor type | Type of conductor and AWG 24/1 conductor cross-section                      |
|                                                           |                | Type of conductor and AWG 24/19 conductor cross-section                     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Conductor type | Type of conductor and stranded 0.25 mm <sup>2</sup> conductor cross-section |
|                                                           |                | Type of conductor and H05V-U0.5 conductor cross-section                     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Requirement    | ≥20 N                                                                       |
|                                                           | Conductor type | Type of conductor and H07V-U1.5 conductor cross-section                     |
|                                                           |                | Type of conductor and H07V-K1.5 conductor cross-section                     |
|                                                           | Conductor type | Type of conductor and AWG 16/1 conductor cross-section                      |
|                                                           |                | Type of conductor and AWG 16/19 conductor cross-section                     |
|                                                           | Evaluation     | passed                                                                      |
|                                                           | Requirement    | ≥40 N                                                                       |

## LSF-SMT 3.81/15/180 3.5SN BK TU

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002643    | ETIM 7.0    | EC002643    |
| ETIM 8.0    | EC002643    | ETIM 9.0    | EC002643    |
| ETIM 10.0   | EC002643    | ECLASS 9.0  | 27-44-04-01 |
| ECLASS 9.1  | 27-44-04-01 | ECLASS 10.0 | 27-44-04-01 |
| ECLASS 11.0 | 27-46-01-01 | ECLASS 12.0 | 27-46-01-01 |
| ECLASS 13.0 | 27-46-01-01 | ECLASS 14.0 | 27-46-01-01 |
| ECLASS 15.0 | 27-46-01-01 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Notes          | <ul style="list-style-type: none"> <li>• Additional push button colours on request</li> <li>• Operating force of slider max. 40 N</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• Wire end ferrule with plastic collar to DIN 46228/4</li> <li>• Wire end ferrule without plastic collar to DIN 46228/1</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool recommended.</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                         |                                                                                                                                                                                                                                                                                                                                                         |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID         | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319230/-T1z1mm-S800/</a> |
| ROHS                    | Conform                                                                                                                                                                                                                                                                                                                                                 |
| UL File Number Search   | UL Website                                                                                                                                                                                                                                                                                                                                              |
| Certificate No. (cURus) | E60693                                                                                                                                                                                                                                                                                                                                                  |

## LSF-SMT 3.81/15/180 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Declaration of the Manufacturer](#)

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[Capacity expansion of LSF-SMT stamping tools](#)  
[Kapazitätserweiterung der Stanzwerkzeuge LSF-SMT](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL DRIVES EN](#)  
[FL ANALO.SIGN.CONV. EN](#)  
[MB SMT EN](#)  
[FL DRIVES DE](#)  
[MB DEVICE MANUF. EN](#)  
[FL BUILDING SAFETY EN](#)  
[FL APPL LED LIGHTING EN](#)  
[FL INDUSTR.CONTROLS EN](#)  
[FL MACHINE SAFETY EN](#)  
[FL HEATING ELECTR EN](#)  
[FL APPL INVERTER EN](#)  
[FL BASE STATION EN](#)  
[FL ELEVATOR EN](#)  
[FL POWER SUPPLY EN](#)  
[FL 72H SAMPLE SER EN](#)  
[PO OMNIMATE EN](#)  
[PO OMNIMATE EN](#)





White paper surface mount technology

[Download Whitepaper](#)

**LSF-SMT 3.81/15/180 3.5SN BK TU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com




**Drawings**
**Product image**

**Dimensional drawing**

**Graph**

**Graph**


The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmueller Interface GmbH & Co. KG

Dimensions without tolerances are no check dimensions




The English version is binding



P=3.81  
SHOWN: LSF-SMT 3.81/04/180

For the mounting on PCBs, it should be noted that the rated data relates only to the PCB components alone.  
The necessary creepage and clearance paths must be observed in the relevant equipment standards in accordance with IEC 664 / VDE 0110.  
The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3.

Weidmüller PCB components are rated in accordance with the DIN EN 61984 standard, and are valid for its field of application.  
If the components are used in accordance with the intended purpose, the components will meet all requirements with respect to the occuring of electrical, mechanical, thermic and corrosive stress.



|    |         |           |
|----|---------|-----------|
| 24 | 87,63   | 3,529     |
| 23 | 83,82   | 3,375     |
| 22 | 80,01   | 3,221     |
| 21 | 76,2    | 3,067     |
| 20 | 72,39   | 2,913     |
| 19 | 68,58   | 2,759     |
| 18 | 64,77   | 2,605     |
| 17 | 60,96   | 2,451     |
| 16 | 57,15   | 2,297     |
| 15 | 53,34   | 2,143     |
| 14 | 49,53   | 1,989     |
| 13 | 45,72   | 1,835     |
| 12 | 41,91   | 1,681     |
| 11 | 38,1    | 1,527     |
| 10 | 34,29   | 1,373     |
| 9  | 30,48   | 1,219     |
| 8  | 26,67   | 1,065     |
| 7  | 22,86   | 0,911     |
| 6  | 19,05   | 0,757     |
| 5  | 15,24   | 0,603     |
| 4  | 11,43   | 0,449     |
| 3  | 7,62    | 0,300     |
| 2  | 3,81    | 0,150     |
| n  | L1 [mm] | L1 [Inch] |

|                                                                                                      |                              |  |                                                                                               |                                                                                                         |                                                                        |            |           |  |
|------------------------------------------------------------------------------------------------------|------------------------------|--|-----------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------|------------|-----------|--|
|  DIN ISO 2768-m | 98688/5<br>23.10.17 HELIS_MA |  | 01                                                                                            | <b>Weidmüller</b>  |                                                                        | Cat.no.: . |           |  |
|                                                                                                      | Modification                 |  | 3 34084  |                                                                                                         |                                                                        |            |           |  |
|                                                                                                      |                              |  |                                                                                               |                                                                                                         | Drawing no.                                                            |            | Issue no. |  |
|                 |                              |  | Date                                                                                          | Name                                                                                                    | Sheet 02 of 07 sheets                                                  |            |           |  |
|                                                                                                      | Drawn                        |  | 22.06.2004                                                                                    | SEIDEL_T                                                                                                | <b>LSF-SMT .../.../180...TU</b><br>LEITERPLATTENKLEMME<br>PCB TERMINAL |            |           |  |
|                                                                                                      | Responsible                  |  |                                                                                               | KRUG_M                                                                                                  |                                                                        |            |           |  |
|                                                                                                      | Checked                      |  | 01.11.2017                                                                                    | HELIS_MA                                                                                                |                                                                        |            |           |  |
| Scale: 5/1                                                                                           | Approved                     |  |                                                                                               | HECKERT_M                                                                                               | Product file: LSF-SMT                                                  |            |           |  |
| Supersedes: .                                                                                        |                              |  |                                                                                               |                                                                                                         | 7358                                                                   |            |           |  |

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260 °C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.

## Recommended reflow soldering profile

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



### Reflow soldering profile

The perfect soldering profile for SMT Surface Mount Technology is one the most exiting question in SMT production. But there are more than one correct answer: The diagram of temperature-on-time is related to processing features of solder paste and to maximum load of components.

We have to consider the following parameters:

- Time for pre heating
- Maximum temperature
- Time above melting point
- Time for cooling
- Maximum heating rate
- Maximum cooling rate

We recommend a typical solder profile with associated process limits. With preheating components and board are prepared smoothly for the solder phase. Heating rate is typically  $\leq +3\text{K/s}$ . In parallel the solder paste is 'activated'. The time above melting point of 217°C the paste gets liquid and components and boards begin to connect. The maximum temperature of 245°C to 254°C should stay between 10 and 40 seconds. In the cooling phase at  $\geq -6\text{K/s}$  solder is cured. Board and components cool down while avoiding cold cracks.